

NEW ! Technology



Zaleta maszyny do depilacji laserowej diody tytanowej 1600 W

1. System usuwania włosów laserem diodowym 755 808 1064 nm wykorzystuje, odpowiedni do wszystkich rodzajów skóry do usuwania włosów.
2. Importowane złote paski laserowe z Niemiec lub USA, maks. 40 000 000 dłuższa żywotność
3. Układ chłodzenia 1600WTEC zapewnia ciągłą pracę lasera bez klimatyzatora latem
4. Bez blizny, bez żadnych skutków ubocznych.
5. Wysoka moc, bez bólu, 3-5 sesji trwałego usuwania włosów

One minute cooling -21°C

Best **TEC Cooling** system
hair remover laser



12*20mm or **12*35mm** handle

Suitable for any unwanted hair on areas like face, arms, armpits, chest, back, bikini, legs...

12*20mm {




12*35mm {



1 minuta zabiegu ☐☐


**NEW !
Technology**





**High-quality
laser bars
imported from
USA**

1000/1200/1600ww high power



Fast hair removal



⌚ 10bar
1000W




⌚ 12bar
1200W



⌚ 16bar
1600W

For all skin types



755nm / 808nm / 1064 nm

The handle equipped with 3 wavelength: Alex 755nm, speed 808nm and long pulse 1064nm

Speed 808nm: Golden standard wavelength for all hair types

Alex 755nm: Specific effective for blonde hair, fine hair

Long Pulse 1064nm: Specific effective for dark, tanned skin



Układ chłodzenia 3 w 1: Chłodzenie powietrzem chłodzenie wodą chłodzenie TEC System 3 w 1

Zdolność do pracy 24 godziny

12*20mm/12*35mm duży rozmiar plamki, skróć czas leczenia dla oryginału 1/5



Large Spot Size

Quick and Comfortable

With large spot size of $1.2 \times 3.5 \text{ cm}^2$, for faster treatments and better patient experience.



TEC Plus

Continuous Contact Cooling

TEC is an advanced technology that continuously cools skin and facilitates range-controlled temperature throughout the entire treatment. Patients can now enjoy a completely pain-free, cool and comfortable experience throughout the session.



- * 12,4/14 cali Prawdziwy kolorowy ekran dotykowy, oferujący super fajne wrażenia dotykowe.
- * Usługa OEM Jest zaakceptowane. parametr regulacji jest w porządku.
- * Dodaj swoje logo i język za darmo

The new 14-inch screen is clear easy to operate.



OEM/ODM SEVRICE

Specyfikacja Urządzenie do depilacji laserem diodowym Titanium 1600W

Przedmiot	Pionowy laser diodowy 755nm808nm1064nm
Typ lasera	Laser diodowy, 10 barów 12 barów/16 barów
Moc każdego paska	100 w/bar
System wyświetlania	Kolorowy ekran dotykowy o przekątnej 12,4/14 cali
Długość fali	808nm/755nm/1064nm
Rozmiar plamki	12*20mm²/12*35mm²
Żywotność uchwytu laserowego	Co najmniej 20-40 milionów strzałów