



**A new
winner
is born!**



**2021 WINNER
EUROPEAN
PRODUCT
DESIGN
AWARD**

V28: Diode Laser hair removal machine

- 1) Stronger, Faster, SmarterHair removal
- 2) New 3D technology 755nm 810nm 1064nm
- 3) Stronger 800/1000/1200/1600watt, 40% faster

Why Choose Us

1. Support fast delivery within three days
2. Minimum 20% payment method
3. Support product appearance customization
4. Two-year warranty



Why all beauty salons, beauticians prefer 808nm diode Laser hair removal machine ?

A) Safer, no side effects on skin and sweat glands, no scar.

B) 755nm+808nm+1064nm suitable for all skin types, black skin and fine hair can be easily treated, suitable to all types.

C) Long laser width, high energy, effective for the hair follicles produce heat accumulation, Permanent hair removal.

D) Quick! Big spot size 12*35mm could prompt the treatment speed, treatment speed and efficiency.


E) Strong cooling system can make momentary epidermal anesthesia, no any painless during.



Large 12*20mm/12*35mm spot size for quick treatment

I-VI skin types and tanned skin safe and painless permanent hair removal

Laser show Handle laser bar optional



Most important thing 3 wavelengths 755+808+1064 covering the optimal treatment.

Painless Proven safety permanent hair removal for all skin types

ICE PLUS continuous cooling system. The treatment process is more comfortable.
It can work continuously for 24 hours.




Just One minute!
Quick cooling down to **-25°C**



Customer Feedback

Treatment Comparison



Screen Display Machine Program

1. 14 inch big screen, quick touch
2. Male & femal, 6 body parts, 6 skin types setting smart software
3. 6 language options, your native language can be added
4. Free OEM program service(language/logo/system/color...)

FREE LOGO SERVICE





14 Years Laser Beauty Decvice Manuafactor

- High Feedback **Top10 Supplier**
- **OEM & ODM SERVICE**



R & D design Design and development teams from the United States and Germany.
 Certified and tested mature production line and quality inspection team and standard production line.
 What we care about most is High-quality products are the standard for maintaining cooperation.

Certificate display

Certificate is the best guarantee for you



Product Paramenters



Model	Diode Laser V28
Laser Type	Germany/USA imported, 10bars,12 bars, 16 bars
Display	14----15.6 inch 4K touchable screen
Wavelength	755nm 808nm 1064nm
Shots	40 million shots
Energy	10~150 j/cm2, adjustable
Frequency	1-10HZ
Cooling	TEC+Air+Water Cooling
Power	3500W
Spot size	12*20mm/12*35mm for choose
Voltage	110V/ 60HZ or 220V/50HZ for choose
Net Weight	95Kg
Gross Weight	105Kg
Machine size	45*52*110cm
Box size	56*70.4*125cm

Delivery time: 3-7 working days after payment


Delivery way: by air, DHL , TNT , Fedex, or delivery agent

Before delivery: testing video and pictures

After delivery Warranty: 2 years,offer impeccable after-sale service

Packing

safe and thoughtful packaging service



Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable,
one-year warranty.

OEM&ODM service for distributor.

Tight packaging

Training: (Video+Manual+Online Service)
Can Keep You Operate It Easily.



3-5 business days delivery

Professional guide:

24 Hours Professional online customer service,

CONTACT US



In terms of following trade details:

- 1)The shipping cost are based on DHL cost to your country
- 2)Delivery time:3-5 days after receiving payments.
- 3)Payment terms:T/T(bank transfer),Western Union.
- 4)Warranty:2 years for the whole machine
- 5)Warranty Policy:one month guarantee replacement (we bear all shipping cost),2years warranty,lifelong maintenance.
- 6)Packing method: Aluminum box with hard plastic foam.
- 7)Free-training to customers:Free We could offer DVD and User's manual and 10 Hours online service to our customers
- 8)Certifications:CE TUV SFDA ISO 13485
- 9)MOQ:1 UNIT
- 10)The quotation here above is valid within 1 month