

Stronger, Faster

×

14-inch HD 4K Screen



Product description

- Permanent removal safe in all skin types; No pain, very comfortable during treatment;
- Suitable for unwanted hair in areas like face, arms, armpits, chest, back, bikini, legs...
- You can choose 808nm or 755 808 1064nm handle, treat all hair color effectively.
- 1 minute cooling fast.Frequency 1-10Hz. Treement Fastly !!! -

NEW



NEW



NEW



For more details of the product, please send us inquiry now.
We have 24-hour online communication service!

Free to be yourself

1 minute of painless hair removal,
Feeling the comfort and coolness that
has never been seen before.

14-inch screen

2 year warranty + work 24 hours



On the cable

350g lightweight **handle**, more ergonomic

Available in **black or white**





35mm



before

after


Large 3.5cm spot size, and integration of three wavelengths
Hair removal is quick, efficient and convenient



One minute cooling -21°C


Best **TEC Cooling** system
hair remover laser

laser rod imported from America. 10million—40million shots. Permanent hair removal



755 808 1064nm Technology is the most advanced technology for all skin removal of different skin..

- * Coherent USA imported laser bar.
- * 10-40 million shots (newest golden laser bar)
- * 10bar 12bar 16bar, to choose from.
- * 1000W / 1200W / 1600W large power,



Treatment effect

Before and After

Treatment comparison





Customer feedback

Ratings & Reviews



m*****a
Georgia

Supplier Service: **Very satisfied** (5 stars)
On-time Shipment: **Very satisfied** (5 stars)

06 Jan 2021



New design 1600W diode laser 755 808 1064 diode la...



Big hug with Maggie, she is very kindness and professional. Weifang Mingliang Electronics Co., Ltd is the best supplier, with high quality and professional packaging.

If you also need laser machine, strongly recommend them.

0



A*****
Mexico

Supplier Service: **Very satisfied** (5 stars)
On-time Shipment: **Very satisfied** (5 stars)

01 Jan 2021



New design 1600W diode laser 755 808 1064 diode la...



estoy muy feliz con mi compra, me llego mi pedido a tiempo con buen empaque, espero que todo marche bien.. Maggy una excelente persona y vendedora espero tener más compras a futuro gracias

0



M*****a

Supplier Service: **Very satisfied** (5 stars)
On-time Shipment: **Very satisfied** (5 stars)

20 Jan 2021



Professional high Power 1600W diode laser hair remo...



super

0



808nm Laser Diode * 14 inch True Color Touching Screen, offering super cool touch experience.

*** Service OEM is accepted. Adjust parameter is OK.**

*** Add your logo and language for free**