

# Stronger, Faster

×

## 14-inch HD 4K Screen



**New unhairing machine -- V23**

**14 inch HD 4K screen**

**Built in different language systems**

**One key setting of parameters for different skin types**

**NEW**



**NEW**



**NEW**



Safe permanent hair removal on all skin types; no pain, very comfortable during the treatment;

Suitable for any unwanted hairs on areas like face, arms, armpits, chest, back, bikini, legs...

You could choose 808nm or 755+808+1064nm handle, Treat all colour hair effectively.

1 minute fast cooling. Frequency 1-10hz. Treatment fastly!!!-

**350g** lightweight **handle**, more ergonomic

Available in **black or white**



One minute cooling **-21°C**



Best **TEC Cooling** system  
hair remover laser



755 808 1064nm Technology is the most advanced technology for all different skin hair removal .

\* USA Coherent imported laser bar.



- \* 10-40 million shots (Newest Golden Laser Bar)
- \* 10bar 12bar 16bar ,to choose from .
- \* 1000w/1200w/1600w big power,

## Before and After

Treatment comparison



**For more product details, please send us inquiry now.  
We have 24-hour online communication service!**