



13 Years Professional Factory!

10 Years Alibaba Golden Supplier!

5.0 High Feedback Point Of Alibaba! ODM/OEM Service!



14 inch
Screen Size



3000W
Input power



1-10HZ
Frequency



755nm 808nm 1064nm
Wavelength

>>Machine 14-inch large screen

>>3000W machine power to ensure the treatment effect

>>1-10Hz fast frequency and 15x25mm spot size ensures faster, smooth and effective treatment

>>808 single wave or 755nm/808nm/1064nm perfect triple wavelengths

>>Easy to operate Data Base system,can do the treatment by man mode and women mode, also different body part.To ensure a safe parameter for new operator

>> Long life time More than 40 millions shots

Gold laser diode module, Anti high temperature.



>>Double filters to keep water quality

>>TEC cooling+ Air Cooling + Water Cooling+Semiconductor cooling
,keep water temperature 26°C-28 °C all the time

>>24 hours continues work

>>Easy to operate Data Base system,can do the treatment by man mode and women mode,

also different body part.To ensure a safe
parameter for new operator

>> Long life time More than 40 millions shots

Gold laser diode module, Anti high temperature.



Product Description



The handle weighs only 350g, which is convenient for treatment

>>12 pieces or 16 pieces Germany Dilas original laser bars,600/800W/1200W power is capable to meet all demands of hair removal on the whole body;

>>1-10Hz fast frequency and 15x25mm spot size ensures faster, smooth and effective treatment;

>>Super sapphire touch cooling system ensures painless and comfortable treatment.

1)Screen can add your own logo

2)screen with 6 languages

3)different body parts for choose, one touch can start your treatment!

CERTIFICATE

