

Diode laser hair removal

© High efficiency © High Power © Safety



755 808 1064 alma laser sopran ice platinum

- * USA or Germany Dilas imported laser bar. (Newest and Best Quality Golden Laser Bar)
- * More than 40 million shots , more than 3 years don't need to change new handle.
- * 755 808 1064nm is for all skin and hair style hair removal

one machine treats more people

24- Hour continuous operation



Continuous Contact Cooling 2 minutes reach -31.3°C , Painless hair removal 24 hours continuously working no any problem

Suit to any color of skin



755nm



808nm



1064nm

Cooling of diode laser

- * Turn on machine, immediately cooling , immediately hair removal
- * Good cooling longer handle lifespan
- * Real ice painless hair removal effect

Hair removal principle




The laser selectively acts on the melanin in the hair follicle, destroying the hair-growing area

Natural hair loss, prevent regeneration, and achieve the purpose of hair removal

Hair removal also stimulates collagen regeneration, shrinks pores and makes skin firm and smooth

- *.3 waves :1064nm +808nm + 755nm, 3 in 1 all skin type can be used
- *.High power: NEW 1000W/ 1200W /1600W//1800W handle for options
- *.Medical handle spot size 12*24mm, 12*36mm, face & body hair removal solution!
- *.Cooling system: Unique Dual- TEC cooling system, most effective to ensure machine work all day, 24hr no down time.
- *.Long life: 40 million shots

Rotated tips, flexible Easily treat areas that are normally hard to reach, including the ears, nostrils and glabella.



12*20mm/12*35mm or 12*24mm/12*36mm spot size suitable for all parts hair removal
3---5 sessions reach ideal hair removal result , permanent hair removal

Suitable for treatment of different body parts

Such as arms, legs, face, armpits, back, chest, etc



Arms



Legs



Face



Armpits





Back



Chest

Clinical Trial Results



The most authentic experience video from customers

It's great for sensitive skin, and I literally didn't feel anything.

It's 40% faster than any other laser as the head is bigger so covers more surface.

The gorgeous stylist sharing her laser experience on this customer

Product display



14 inch big touch screen of diode laser 755 808 1064 alma laser sopran ice platinum

* man and woman choice for all parts hair removal

*Any language you wanted

*Free logo service

*customized screen service

Parameters Table

Device Name	Diode Laser Machine
Model Number	Diode Laser V35
Wavelength	755+808+1064nm Technology
Screen size	14 inch 4K Style touch screen
Lifetime	40 Million shots
Pulse Duration	1-200ms (10/12) 1-300ms (16)
Laser Bar	120w for each 1 , USA Coherent Laser Bar
Frequency	1-10hz
Spot size	12x24mm or 12x36mm Spot Size
Energy	1-150J
Cooling System	Compressor+ Water circulation
Power Of Machine	3500W
Voltage	AC220V 50HZ/AC110V 60HZ
Package Size	110*56*70cm
Package	Aluminum box
Warranty	2 years for machine , 1 year for handle

OEM / ODM Service , Any style , any color you wanted
More details are welcome to consult!