



Painless 810nm-755nm *V2.9*
Diode laser handle
Suitable for all skin tones and body parts


- *1800w High power diode laser with nice cooling technology, for hair removal with painless!
- * Diode laser enable the light to penetrate deeper into skin and safer than other laser. because it can avoid the melanin pigment into the skin's epidermis, we can use it for the permanent hair removal of all color hairs on all 6 kinds skin types.
- * Suitable for any unwanted hair on areas like face, arms, armpits, chest, back, bikini, legs...It also have the skin renewing.
- * Frequency 1-10hz. treatment fastly!!! Machine for fast and permanent hair removal . Painless!!




755 nm



808 nm




1064 nm



755 nm for white skin (fine, golden hair removal);



808 nm for yellow neutral skin (brown hair removal);



1064 nm for black skin (black hair removal)

Handle display

1. Three wavelength diode laser.
2. Golden laser bars from German or USA improved 40,000,000+ longer lifespan.
3. Safe, Fast, Painless permanent
4. For all skin and hair style hair removal
5. 14.0 inch true color touch screen with 6 skin colors.

Handle Details

Three Wavelengths Work Together



Waves laser combines 755nm 808nm 1064nm, suits for all skin and hair types treatment.

755nm for white skin (fine/ golden hair) hair removal.

808nm for yellow (natural) skin hair removal.

1064nm for black skin (black hair) hair removal.

For all skin types

Triple wavelength laser work together

755
nm

808
nm

1064
nm

755nm/808nm/1064nm

755nm
808nm
1064nm

Laser hair removal treatment theory



Hair active growth
phase(3-6years)



laser treatment



Transition phase
(1-2weeks)



Resting phase
(1-2 weeks)



Return to growth
phase

Product Paramenters







Model	808V29
Laser Type	808nm diode laser or 755/808/1064nm 3 waves combined
Display	14 inch 4K touchable screen
Wavelength	755/808/1064
shots	20-40 million shots
Energy	10~150 j/cm2, adjustable
Frequency	1-10HZ
Cooling	Compressor+air+water
Power	3500W
Spot size	12*20mm or 12*35mm for choose
Voltage	110V/ 60HZ or 220V/50HZ for choose
Net Weight	95Kg
Gross Weight	105Kg
Machine size	53*40*105cm

Box size 125*56*70.4

Before and after effect comparison

Before and After



Before



After



Before



After



Before



After



Before



After

Painless hair removal, no side effect□Make your skin silky and full of charm!

Operation System

- * 14.0 inch screen
- * multi-language system
- * Easy to operateproviding operation skills and teaching services
- *Free logo and language can be customized on the scr

Custom Section

LOGO design



SYSTEM design



Custom section

You can customize your exclusive logo screen according to your needs

Why Choose Us

Our customers

60000+ CUSTOMERS



102

Countries

OEM/ODM

Customize the machine according to customer needs

CERTIFICATE



15 years manufacturer with rich experience in producing beauty machines!

14 years Alibaba golden supplier

CE certificates approved TUV certificates approved

Personal custom made & OEM

Product packaging

The aluminum box packaging machine is sturdy and durable, with safety protection, helping your machine get home safely!

PACKING

Safe and thoughtful packaging service



Built-in prevention
collision bubble

Two- year warranty for machine
handle as consumable,
one-year warranty

Tight packaging

Training:
(video +manual+online service)
can keep you operate it easily



3-5 business days
delivery

professional guide:
24 hours professional online
customer service