

# Diode Laser

*ice* Hair removal



## **1200W + 1800W Sopran Titanium hair removal machine**

1. Diode Laser technical, suits for all skin and hair types.
2. Handles: Spot size 12\*24mm, the other 12\*36mm
3. Fast treatment: 1-10Hz frequency, Germany imported laser bars.

**Air + water + compressor refrigeration**

**Ice sensation treatment, comfortable and painless**



**Super cooling effect, the handle temperature can be reduced to -25 °C**

### **Handle of Soprano Titanium hair removal machine**

1.12\*24mm handle can you on small parts of the body, such as face hair removal and other samll place.

2.12\*36mm can use at large parts of the body, such as back, arms and legs.....

**Arm** hair removal



**Lip** hair removal



**Face** hair removal



**Leg** hair removal



**Back** hair removal



**Underarm** hair removal



**Bikini** hair removal



**Triple wavelength included:755nm 808nm 1064nm**

755nm suitable for light skin hair removal .

808nm suitable for neutral skin hair removal .

1064nm suitable for black skin hair removal .

Medical 1200W/1800W

**50 Million Shots**

**USA / Germany Imported Laser Bar**



**755nm+808nm+1064nm**



**ALEX 755nm**

**For white skin**

(fine, golden hair removal )



**SPEED 810nm**

**For yellow neutral skin**

(brown hair removal)



**YAG 1064nm**

**For black skin**


(black hair removal)

**10bars 1200W+15bars 1800W diode laser:**

**\* Germany Dilas imported laser bar. (Newest and Best Quality Golden Laser Bar)**

**\* Shots: 20-50 million shots time**

**\* 755 808 1064nm is for all skin and hair style hair removal**



### Screen Display

- 1) Big size: used 14 inch color touch screen.
- 2) Multiple language: three kinds of skin types option,easy to operate.
- 3) OEM service: your logo can be added on machine screen for free,accept your special language.