

Diode Laser

ice Hair removal




1200W + 1800W Sopran Titanium hair removal machine

1. Diode Laser technical, suits for all skin and hair types.
2. Handles: Spot size 12*24mm, the other 12*36mm
3. Fast treatment: 1-10Hz frequency, Germany imported laser bars.

Air + water + compressor refrigeration

Ice sensation treatment, comfortable and painless



Handle of Soprano Titanium hair removal machine

1.12*24mm handle can you on small parts of the body, such as face hair removal and other samll place.

2.12*36mm can use at large parts of the body, such as back, arms and legs.....

Arm hair removal



Face hair removal



Lip hair removal



Back hair removal



Leg hair removal



Bikini hair removal



Underarm hair removal



Triple wavelength included: 755nm 808nm 1064nm

755nm suitable for light skin hair removal .

808nm suitable for neutral skin hair removal .

1064nm suitable for black skin hair removal .

Medical 1200W/1800W

50 Million Shots

USA / Germany Imported Laser Bar



755nm+808nm+1064nm



ALEX 755nm

For white skin

(fine, golden hair removal)



SPEED 810nm

For yellow neutral skin

(brown hair removal)



YAG 1064nm

For black skin


(black hair removal)

10bars 1200W+15bars 1800W diode laser:

*** Germany Dilas imported laser bar. (Newest and Best Quality Golden Laser Bar)**

*** Shots: 20-50 million shots time**

*** 755 808 1064nm is for all skin and hair style hair removal**



Screen Display

- 1) Big size: used 14 inch color touch screen.
- 2) Multiple language: three kinds of skin types option,easy to operate.
- 3) OEM service: your logo can be added on machine screen for free,accept your special language.