

Soprano Ice Titanium

Painless hair removal. For you, for life!



Why Choose Us

Why all Salons, beauty salons, beauticians prefer 808nm diode Laser hair removal machine ?

- A) Safer, no side effects on skin and sweat glands, no scar.
- B) 755nm+808nm+1064nm suitable for all skin types, black skin and fine hair can be easily treated, suitable to all types.
- C) Long laser width, high energy, effective for the hair follicles produce heat accumulation, Permanent hair removal.
- D) Quick! Big spot size 12*36mm could prompt the treatment speed, treatment speed and efficiency.
- E) Strong cooling system can make momentary epidermal anesthesia, no any painless during.

350g

Ultra light handle



12×36mm

Handle

1800W diode laser hair removal



12×24 mm

Handle

1200W diode laser hair removal

ice titanium 808nm diode laser hair removal machine
Large 12*24mm/12*36mm spot size for quick treatment
I-VI skin tones and tanned skin□safe and painless permanent hair removal

Soprano



755

808

1064

3 Wavelengths



Painless Proven
safety permanent
hair removal .

All skin
types
eventanned skin



12*24mm



12*36mm



ICE PLUS continuous cooling system. The treatment process is more comfortable.
It can work continuously for 24 hours.



Just One minute!
Quick cooling down to

-25°C



The latest plug-in design can treat difficult to reach small body parts.
Such as nose, eyebrows, auricles, etc.

New breakthrough!



360 ° Rotatable

6.8×6.8mm

Handle


1200W diode laser hair removal

Improved Reach: **360 ° Rotatable**

Easily treat areas that are normally hard to reach,
including the ears, nostrils and glabella.

Customer Feedback

Treatment Comparison





Screen Display Machine Program

1. 14 inch big screen, quick touch
2. Male & femal, 6 body parts, 6 skin types setting smart software
3. 6 language options, your native language can be added
4. Free OEM program service(language/logo/system/color...)

14inch true touch screen
6 kinds skin type for choice. accept ODM OEM Service.

The new **14-inch** screen is clear easy to operate.



Advantage of: soprano ice laser hair removal machine

Super cooling: air + water+TEC condenser cooling system,
Which keep water temperature in 25-28°C, continuous work in summer.
Germany imported laser: 12 laser bars handle, 10-40 million shots.
Big spot size 15x25mm, 12*38mm, 1200 w high power to sure fast hair removal.
Italian water pump: more better for the laser water circulate
Painless and no side effect.



14 Years Laser Beauty Decvice Manuafactor

- High Feedback **Top10 Supplier**
- **OEM & ODM SERVICE**



R & D design Design and development teams from the United States and Germany.
Certified and tested mature production line and quality inspection team and standard
production line.

What we care about most is High-quality products are the standard for maintaining
cooperation.

Certificate display

Certificate is the best guarantee for you



Product Parameters

| | |
|--------------|---|
| Model | Medical V19 |
| Laser Type | Germany/USA imported, 12 bars, 15 bars |
| Display | 14---15.6 inch 4K touchable screen |
| Wavelength | 755nm 808nm 1064nm |
| Shots | 40 million shots |
| Energy | 10~150 j/cm2, adjustable |
| Frequency | 1-10HZ |
| Cooling | High Speed Double TEC coolingAir and Close Water Circulation Treatment head with semiconductor cooling temperature adjustable |
| Power | 3500W |
| Spot size | 12*24mm/12*36mm for choose |
| Voltage | 110V/ 60HZ or 220V/50HZ for choose |
| Net Weight | 95Kg |
| Gross Weight | 105Kg |
| Machine size | 45*52*110cm |
| Box size | 56*70.4*125cm |

Delivery time: 3-7 working days after payment

Delivery way: by air, DHL , TNT , Fedex, or delivery agent


Before delivery: testing video and pictures

After delivery Warranty: 2 years,offer impeccable after-sale service

Packing And Shipping

Packing

safe and thoughtful packaging service



Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable,
one-year warranty.

OEM&ODM service for distributor.

Tight packaging

Training: (Video+Manual+Online Service)
Can Keep You Operate It Easily.



3-5 business days delivery

Professional guide:
24 Hours Professional online customer service,

CONTACT US



In terms of following trade details:

- 1)The shipping cost are based on DHL cost to your country
- 2)Delivery time:3-5 days after receiving payments.
- 3)Payment terms:T/T(bank transfer),Western Union.
- 4)Warranty:2 years for the whole machine
- 5)Warranty Policy:one month guarantee replacement (we bear all shipping cost),2years warranty,lifelong maintenance.
- 6)Packing method: Aluminum box with hard plastic foam.
- 7)Free-training to customers:Free We could offer DVD and User's manual and 10 Hours online service to our customers
- 8)Certifications:CE TUV SFDA ISO 13485
- 9)MOQ:1 UNIT
- 10)The quotation here above is valid within 1 month