

Diode Laser



15 Bar **1800W** Handle

*Increase the treatment head of nasal hair
and treat small parts easily



Diode laser hair removal machine.

- * No pigmentation. Suitable for any kind of skin;
- * Suitable for any kind of skin ;
- * Safe and Fast.
- * International Hair Removal Golden Standard;
- * The optimal laser wavelength 808nm or 755+808+1064nm;

350g

Ultra light handle



12×36mm

Handle

1800W diode laser hair removal



12×24 mm

Handle


1200W diode laser hair removal

Three Waves laser combines 755nm 808nm 1064nm, suits for all skin and hair types treatment.

755nm for white skin (fine/ golden hair) hair removal.

808nm for yellow (natural) skin hair removal.

1064nm for black skin (black hair) hair removal.



Smayer
Shandong Smayer Electronics CO.,LTD




ALEX 755nm
For white skin
 (fine, golden hair removal)




SPEED 810nm
For yellow neutral skin
 (brown hair removal)



YAG 1064nm
For black skin
 (black hair removal)



Treatment Comparison





Emergency
stop button

12 inch big screen
quick touch
easy operate

Diode laser handle

Vents

Plug