




Advantages


- 1. 3 waves Yag 1064nm + Diode 808nm + Alex 755nm, 3 in 1 all skin type can be used
High power: NEW 1000W/ 1200W /1600W handle for options
- 2. Big spot size 12*20mm, 12*38mm, face & body hair removal solution!
- 3. Cooling system: Unique Dual- TEC cooling system, most effective to ensure machine work all day, 24hr no down time.
- 4. Long life: double life support guarantee



A natural



B energy absorbed by hair



C hair follicle died

Safe Use On All Skin Type

Alex 755nm for light skin

Speed Diode 808nm for yellow skin

Long Pulse 1064nm for darker skin


Handle Details

Three Wavelengths Work Togher




12*20nm

755nm Laser
808nm Laser
1064nm Laser



12*35nm

755nm Laser
808nm Laser
1064nm Laser



Features & Diode Laser

1. Laser bar: Imported laser bar US Coherent/ Dilas brand
2. 3 waves: 755nm 808nm 1064nm 3 in 1
3. Spot size: 12*20mm, 12*35mm
4. Power: High power 1000W 1200W 1600W & OEM
3. Cooling: Super cooling start frozen in 1 minutes, 24 hr continue work



Pain-free Guarantee

Super TEC cooling system.Fast cooling 1 minute frozen.Lowest temperature -22°C

Before and After

Treatment comparison



Software & Program

1. Easy Start: Based on male & female/6 body parts, Add 6 skin types setting smart software
2. 6 language options, your native language can be added
3. OEM program service available (logo/system...)

Custom Section

CASE design



LOGO design



SYSTEM design



CERTIFICATE DISPLAY

