



**Diode laser hair removal machine.**

- \* No pigmentation. Suitable for any kind of skin;
- \* Suitable for any kind of skin ;
- \* Safe and Fast.
- \* International Hair Removal Golden Standard;
- \* The optimal laser wavelength 808nm or 755+808+1064nm;

**350g**

Ultra light handle



12×36mm

**Handle**

1800W diode laser hair removal



12×24 mm

**Handle**


1200W diode laser hair removal

**Three Waves laser combines 755nm 808nm 1064nm, suits for all skin and hair types treatment.**

755nm for white skin (fine/ golden hair) hair removal.

808nm for yellow (natural) skin hair removal.

1064nm for black skin (black hair) hair removal.






**ALEX 755nm**  
**For white skin**  
 (fine, golden hair removal )




**SPEED 810nm**  
**For yellow neutral skin**  
 (brown hair removal)



**YAG 1064nm**  
**For black skin**  
 (black hair removal)



## Treatment Comparison





Emergency  
stop button

12 inch big screen  
quick touch  
easy operate

Diode laser handle

Vents

Plug

**If you need help to know more, welcome to consult!**