

NEW ARRIVALS

2022 Newest Permanent and Painless Ice Hair Removal

- 3 waves 1064nm+808nm+755nm,
- 3 in 1 all skin type can be used
- Imported gold laser bar, Shots up to 40 million+



12*20mm



12*35mm



- * USA or Germany Dilas imported laser bar. (Newest and Best Quality Golden Laser Bar)
- * More than 40 million shots , more than 3 years don't need to change new handle.
- * 755 808 1064nm is for all skin and hair style hair removal

Newest **Factory Lowest Price** Diode Laser Hair Removal

**A new
winner
is born!**



HD 4K Screen Design

The screen can be rotated for more convenient operation

One-touch start button

Continuous Contact Cooling 2 minutes reach -31.3°C , Painless hair removal 24 hours continuously working no any problem

ULTRA-LOW
Temperature
-31°C

Ultra low temperature
protect skin
not burned by the laser



Cooling of ice platinum

- * turn on machine, immediately cooling , immediately hair removal
- * good cooling longer handle lifespan
- * real ice painless hair removal effect

MULTI-ANGLE MACHINE DISPLAY

New upgrade 14-inch HD 4K screen

The screen can be rotated 180 degrees

12*35mm big spot size

Optional parameters for different skin types



*.3 waves :1064nm +808nm + 755nm, 3 in 1 all skin type can be used

*.High power: NEW 1000W/ 1200W /1600W//1800W handle for options

*.Medical handle spot size 12*24mm, 12*36mm, face & body hair removal solution!

*.Cooling system: Unique Dual- TEC cooling system, most effective to ensure machine work all day, 24hr no down time.

*.Long life: 40 million shots

Three Simultaneous Wavelengths in one Applicator

4cm²
12mm*20mm / 12mm*35

Mix Laser 755nm+808nm+1064nm
Multiple Laser Wavelengths and Technologies

Alex 755nm
Ideal for range of hair colors

Speed 808nm
Safe for darker skin types

YAG 1064nm
Perfect solution for darker skin

Rotated tips, flexible Easily treat areas that are normally hard to reach, including the ears, nostrils and glabella.

Simple installation
and easy handling of areas that are usually difficult to reach

12x24mm
1200W
big power

Improved Reach:
360 ° Rotatable

Easy installation


Finger treatment

Nose hair treatment

Ear treatment

Eyebrow treatment

Treatment effect



12*20mm/12*35mm or 12*24mm/12*36mm spot size suitable for all parts hair removal
3---5 sessions reach ideal hair removal result , permanent hair removal



The most authentic experience video from customers

It's great for sensitive skin, and I literally didn't feel anything.

It's 40% faster than any other laser as the head is bigger so covers more surface.

The gorgeous stylist sharing her laser experience on this customer



For all skin and hair style hair removal

You will see good results after 3 treatments.

* Painless * Fast * No downtime * No side-effects

Screen Display

14 inch big touch screen of diode laser 755 808 1064

* man and woman choice for all parts hair removal

*Any language you wanted

*Free logo service

*customized screen service

OEM / ODM Service , Any style , any color you wanted

More details are welcome to consult!