

 **Smayer**

**A new
winner
is born!**



**2021 WINNER
EUROPEAN
PRODUCT
DESIGN
AWARD**

V28: Diode Laser hair removal machine

- 1) Stronger, Faster, SmarterHair removal
- 2) New 3D technology 755nm 810nm 1064nm
- 3) Stronger 800/1000/1200/1600watt, 40% faster



Why all beauty salons, beauticians prefer 808nm diode Laser hair removal machine ?

A) Safer, no side effects on skin and sweat glands, no scar.

B) 755nm+808nm+1064nm suitable for all skin types, black skin and fine hair can be easily treated, suitable to all types.

C) Long laser width, high energy, effective for the hair follicles produce heat accumulation, Permanent hair removal.

D) Quick! Big spot size 12*35mm could prompt the treatment speed, treatment speed and efficiency.

E) Strong cooling system can make momentary epidermal anesthesia, no any painless during.

About Handles




Ice titanium 808nm diode laser hair removal machine

Large 12*20mm/12*35mm spot size for quick treatment

I-VI skin types and tanned skin safe and painless permanent hair removal

Laser show Handle laser bar optional



Most important thing 3 wavelengths 755+808+1064 covering the optimal treatment painless proven safety permanent hair removal

For all skin types

ICE PLUS continuous cooling system. The treatment process is more comfortable.

It can work continuously for 24 hours.



Just One minute!
Quick cooling down to **-25°C**



Screen Display Machine Program

1. 14 inch big screen, quick touch
2. Male & femal, 6 body parts, 6 skin types setting smart software
3. 6 language options, your native language can be added
4. Free OEM program service(language/logo/system/color...)

FREE LOGO SERVICE





14 Years Laser Beauty Decvice Manuafactor

- High Feedback **Top10 Supplier**
- **OEM & ODM SERVICE**



R & D design Design and development teams from the United States and Germany.
 Certified and tested mature production line and quality inspection team and standard production line.
 What we care about most is High-quality products are the standard for maintaining cooperation.

Certificate display

Certificate is the best guarantee for you



Product Paramenters



| | |
|--|---|
| Model | Diode Laser V28 |
| Laser Type | Germany/USA imported, 10bars,12 bars, 16 bars |
| Display | 14---15.6 inch 4K touchable screen |
| Wavelength | 755nm 808nm 1064nm |
| Shots | 40 million shots |
| Energy | 10~150 j/cm2, adjustable |
| Frequency | 1-10HZ |
| Cooling | TEC+Air+Water Cooling |
| Power | 3500W |
| Spot size | 12*20mm/12*35mm for choose |
| Voltage | 110V/ 60HZ or 220V/50HZ for choose |
| Net Weight | 95Kg |
| Gross Weight | 105Kg |
| Machine size | 45*52*110cm |
| Box size | 56*70.4*125cm |
| Delivery time: 3-7 working days after payment | |
| Delivery way: by air, DHL , TNT , Fedex, or delivery agent | |
| Before delivery: testing video and pictures | |
| After delivery Warranty: 2 years,offer impeccable after-sale service | |

Packing And Shipping

Packing

Safe and thoughtful packaging service



Tight packaging

The machine shall be made of waterproof materials and packaged

**Anti collision foam board
inside aluminum box**



3-5 business days delivery

Professional guide:

24 Hours Professional online customer service

CONTACT US



In terms of following trade details:

- 1)The shipping cost are based on DHL cost to your country
- 2)Delivery time:3-5 days after receiving payments.
- 3)Payment terms:T/T(bank transfer),Western Union.
- 4)Warranty:2 years for the whole machine
- 5)Warranty Policy:one month guarantee replacement (we bear all shipping cost),2years warranty,lifelong maintenance.
- 6)Packing method: Aluminum box with hard plastic foam.
- 7)Free-training to customers:Free We could offer DVD and User's manual and 10 Hours online service to our customers
- 8)Certifications:CE TUV SFDA ISO 13485
- 9)MOQ:1 UNIT
- 10)The quotation here above is valid within 1 month