



NEW


Portable Diode Laser

**Dealer's price permanent laser hair removal diode laser hair removal machine
Germany 755 808 1064 diode laser diode ipl laser hair removal**



Advantages

- * USA or Germany imported laser bar 10bars/15bars
- * More than 50 million shots , more than 3 years don't need to change new handle.
- * 3 waves 1064nm +808nm + 755nm, 3 in 1 all skin type can be used



Products Description

Mini Portable

The net weight of the handle is
about equal to one iphone

285g

Ergonomic handle
It's not tiring to take off



About Handle

1200W/1800W big power for free choice

12*24 or 12*36mm spot size

*285g Medical handle, light weight, free quick slide treatment


* With indicator light, to show working condition(on machine & handle), safely use

EXFU

Exfu Violin

One-of-a-kind styling
Build your own hair removal machine

One minute cooling, 12x24cm²super cool area.
Newest design handle 0.31kg



1 minute quick frosting, comfortable and painless treatment experience

EXFU[®]
Simple • Safe • Enjoy

What can
we do
in
1 MINUTE

Time for a cup of instant coffee,
the handle can quickly frost.





800/1000/1200/1600W

50 Million Shots

USA / Germany Imported Laser Bar

755nm+808nm+1064nm



ALEX 755nm

For white skin

(fine, golden hair removal)



SPEED 810nm

For yellow neutral skin

(brown hair removal)





YAG 1064nm

For black skin

(black hair removal)

755+808+1064nm, suitable for permanent hair removal of all skin types



Ingenious details I am better than others

Product detail
layout



Surround light strip

Cool lighting effect
not dazzling



Newest design handle 0.31kg

One minute cooling
Customizable glowing logo



One-of-a-kind styling

Ingenious production
focus on details



Model	Exfu diode laser
Laser Type	Germany/USA imported, 8---12bars, 800W---1200W
Display	14 inch 4K touchable screen
Wavelength	808nm or 755nm 808nm 1064nm
shots	50 million shots
Energy	10~150 j/cm2, adjustable
Frequency	1-10HZ
Cooling	High Speed Double TEC coolingAir and Close Water Circulation Treatment head with semiconductor cooling temperature adjustable
Power	3500W
Spot size	12*24mm or 12*36mm for choose
Voltage	110V/ 60HZ or 220V/50HZ for choose
Net Weight	35Kg
Gross Weight	45Kg

7 * 24 hour online service!

Welcome to consult!