The advertisement features a woman with curly hair on the left and a black laser machine on the right. The machine has a screen at the top and a '50% OFF' sticker. Text in the center promotes it as the 'NEWEST COMING, FASTEST STRONGEST, DOUBLE HAIR REMOVAL SYSTEM' with '1200W + 1800W TITANIUM COMING' and a 'VIEW MORE' button.

GENES LASER

NEWEST COMING, FASTEST
STRONGEST, DOUBLE HAIR
REMOVAL SYSTEM

1200W + 1800W TITANIUM COMING

[VIEW MORE](#)

*1800w High power diode laser with nice cooling technology, for hair removal with painless!

*Diode laser enable the light to penetrate deeper into skin and safer than other laser. because it can avoid the melanin pigment into the skin's epidermis, we can use it for the permanent hair removal of all color hairs on all 6 kinds skin types.

*Suitable for any unwanted hair on areas like face, arms, armpits, chest, back, bikini, legs...It also have the skin renewing.

*Frequency 1-10hz. treatment fastly!!! Machine for fast and permanent hair removal . Painless!!

Handle display

① Optional 12*24mm/12*36mm light spot size.

Different spot size meet different body parts hair removal needs .



*spot size : 12*24mm*



*spot size : 12*36mm*

② 10bars 1200w / 15bars 1800w. 10million—40million shots.

Effective for permanent hair removal

③ 755nm and 808nm and 1064nm , suits for all skin and hair types.

Cooling effect

The handle has a cooling effect that improve treatment comfort.



*spot size : 12*24mm*



*spot size : 12*36mm*

Waves laser combines 755nm 808nm 1064nm, suits for all skin and hair types

treatment




755nm for white skin (fine/ golden hair) hair removal


808nm for yellow (natural) skin hair removal

1064nm for black skin (black hair) hair removal


diode laser hair removal machine

working principle


| | |
|---|---|
|  | 755 nm for white skin (fine, golden hair removal); |
|  | 808nm for yellow neutral skin (brown hair removal); |
|  | 1064nm for black skin (black hair removal) |



A natural




B energy absorbed by hair



C hair follicle died

working principle


Triple wavelength laser spots work together




Before and after effect comparison

Scope of application

Suitable for any unwanted hair on areas like face, arms, armpits, chest, back, bikini, legs...



CE and TUV CERTIFICATE




**U.S. FOOD & DRUG
ADMINISTRATION**

[Home](#)
[Food](#)
[Drugs](#)
[Medical Devices](#)
[Radiation-Emitting Products](#)
[Vaccines & Blood](#)

510(k) Premarket Notification

[FDA Home](#)
[Medical Devices](#)
[Databases](#)



510(k) | Defenses | Registration & Listing | Adverse Events | Recall

CPR Title 21 | Radiation-Emitting Products | X-Ray Accessories

[New Search](#)

| | |
|------------------------------|--|
| Device Classification Name | Crossed Laser Gun |
| 510(k) Number | K090295 |
| Device Name | Medical Grade Laser |
| Applicant | Wavelength Medical 140 N. 124th, Youngstown Youngstown, OH 44510 LJ Mingling |
| Applicant Contact | Beijing Beilong Medical Room 512, Building 1 Fangshan District Beijing, CN 102404 |
| Correspondent | May Wang |
| Correspondent Contact | 525 1613 |
| Registration Number | 03020003 |
| Classification Product Code | 09270029 |
| Date Received | Substantially Equivalent |
| Decision Date | General & Plastic Devices |
| Decisions | 1106 Review Panel |
| Regulation Medical Specialty | Traditional |
| Y106 Review Panel | No |
| Reviewed By Third Party | No |
| Combination Product | No |

Certificate of Compliance

No. 041/1030/EMC/CEC
 Technical Contributor No. 104/2012/10/EMC/CEC

Certificate's Holder: Welling Minglong Electronics Co., Ltd.
 Floor 3, Workshop 2, No.13626, Yuting East Street,
 Yuting Community, Xincheng Street, High-tech Zone,
 Wuxi, Jiangsu, Jiangsu, China.

Certification ECM Mark: 

Product: LASER BARCODE DEVICE
Model(s): See the following (s)

Verification to: Standard: EN 60951-1:2006+A2:2011
 EN 60951-2:2012/IEC 60951-2:2006+A2:2011
 referred to CE Declaration:
 Standard Declaration K9404R1C3207/1/EN

Remarks: The product has been verified on a voluntary basis. The product(s) within the attachment of the certificate must be affixed to in accordance to the above listed standards. The above Compliance mark can be affixed on the product(s) according to the CE regulation, although its issuance and use of the regulation can be found at <http://www.emccouncil.com>. The Certificate of Compliance can only be checked for validity on www.emccouncil.com.

CE  

Issue on 22/ December 2012 Valid until 21/ December 2014

EMC Council  

EMC
 (1) www.emccouncil.com (2) emccouncil@emccouncil.com
 www.emccouncil.com www.emccouncil.com


Measurement Systems Certification Body No. 2002
Institute for Testing and Certification
T. Bělá 206, 754 21 Zlín, Czech Republic
www.itc.cz

CERTIFICATE
No. 10 0144 SJ

We confirm on the basis of a performed audit that company

Weifang Mingliang Electronics Co.,Ltd.
338Wang Fang Dongjia Street Wafang Circle
Company Reg. No.: 3707030000004

has implemented and documented a functional quality management system
in compliance with the requirements of the standard

EN ISO 13485:2003

Covering the following activities:

**Design & Development, Production and Distribution of IP, Phototherapy System,
Model: VAG-Q Switched Laser and RF Device**

The Certificate is based on the basis of the results mentioned in Audit Report No.
20100400003170. The Certificate validity is conditioned to positive results of surveillance audits
which the certified company undertakes in regular

Paul Vög


Date of Issue: 01.01.2010
Valid until: 31.01.2013
Date of the last certification audit: 04.07.2007

By: Peter Haid
Head of Certification Body



SHIPPING

Welcome to visit our factory



In terms of following trade details:

- 1)The shipping cost are based on DHL cost to your country
- 2)Delivery time:3-5 days after receiving payments.
- 3)Payment terms:T/T(bank transfer),Western Union.
- 4)Warranty:2 years for the whole machine
- 5)Warranty Policy:one month guarantee replacement (we bear all shipping cost),2years warranty,lifelong maintenance.
- 6)Packing method: Aluminum box with hard plastic foam.
- 7)Free-training to customers:Free We could offer DVD and User's manual and 10 Hours online service to our customers
- 8)Certifications:CE TUV ISO 13485
- 9)MOQ:1 UNIT
- 10)The quotation here above is valid within 1 month