

2021 Salon Queen

FASTER: 60% FASTER
STRONGER: STRONGER POWER 40%
BETTER RESULT
SMARTER: 4K ANDROID SCREEN

FASTER, STRONGER, SMARTER

1. Three wavelength diode laser.
2. Golden laser bars from German or USA improved 40,000,000+ longer lifespan.
3. Safe, Fast, Painless, permanent
4. For all skin and hair style hair removal
5. 14.0 inch true color touch screen with 6 skin colors.
6. Two models can be selected, single handle or double handle



2021 Salon Queen

FASTER, STRONGER, SMARTER

Most advanced TEC cooling system inside this machine to deliver a super good cooling results. 24 hours working time. Sapphire material. Actual Pain-free experience!

- 1) 10 bars/ 12 bars/ 16 bars, 10-40 million shots.
- 2) Big spot 12*20mm / 12*35mm for fast hair removal.
- 3) Frozen ice cooling sapphire crystal, for painless hair removal.
- 4) High quality gold laser bar imported from Germany.
- 5) Medical handle as low as 350g easy to treatment.

Screen system

1. 14 inch big touch screen, humanized designed.
2. Male/female, body parts, 6 skin types for option.
3. 6 language systems, native language + whatever you want.
4. Free OEM program service (logo/system...)

| | |
|-------------------------|--|
| Laser bar | Germany/USA imported, 8 bar, 10 bar, 12 bars, 16 bars |
| Wavelength | 755nm 808nm 1064nm/ or single 808nm |
| Energy | 0-150J/cm ² |
| Frequency | 1-10hz |
| Pulse width | 40-800ms |
| Operative LCD Interface | 14.0 TFT True Color LCD touch screen |
| Cooling system | Air and Close Water Circulation Treatment head with semiconductor cooling temperature adjustable |
| Power | 4000W |
| Electrical source | 220V/50HZ or 110V/60HZ |
| N.W/ G.W | 62kg/78kg |

Company Strength



- >>OEM your own machine body.
- >>OEM your own program software.
- >>OEM pretty machine colors.
- >>Print your LOGO on machine body and screen.

Custom Section


CASE design



LOGO design



SYSTEM design



Certificate Display

CERTIFICATE DISPLAY



Packing

safe and thoughtful packaging service



Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable,
one-year warranty.

OEM&ODM service for distributor.

Tight packaging

Training: (Video+Manual+Online Service)
Can Keep You Operate It Easily.



3-5 business days delivery

Professional guide:
24 Hours Professional online customer service,

