



### Handle features of Diode laser hair removal :

- »»USA laser bar, 12 bars, high power 1200w
- »»TEC condenser cooling system: 2 big 1200W TEC condensers, keep the water constantly at 24°C, ensures the machine working continuously without stopping
- »»Super Cooling effect: Sapphire Temperature-5~3°C. Effectively reduce the painful in the treatment and make
- »»Italy Water Pump: more better for laser water circle, take away heat, longer life time.
- »»Two water filters:two food grade exchange resin,can ensure the water quality for circulation

# Harmony XL PRO

DIODE LASER HAIR REMOVAL



13 YEARS FACTORY, 2 YEARS WARRANTY,  
102 COUNTRIES,  
60,000+ CUSTOMERS

Make Your Beauty Business  
More Easier.






## Small Spot Size

### Quick and Comfortable

With spot size of  $1.2 \times 2.0 \text{ cm}^2$ , for faster treatments and better patient experience.




## TEC Plus

### Continuous Contact Cooling

TEC is an advanced technology that continuously cools skin and facilitates range-controlled temperature throughout the entire treatment. Patients can now enjoy a completely pain-free, cool and comfortable experience throughout the session.

## For all skin types



755nm / 808nm / 1064 nm



»»Super Cooling effect:Sapphire Temperature-5~3°C. Effectively reduce the painful in the treatment and make

»»Italy Water Pump:more better for laser water circle, take away heat, longer life time.

»»Two water filters:two food grade exchange resin,can ensure the water quality for circulation

### Hair removal principle

Make Your Beauty Business More Easier



The laser selectively acts on the melanin in the hair follicle, destroying the hair-growing area

Natural hair loss, prevent regeneration, and achieve the purpose of hair removal

Hair removal also stimulates collagen regeneration, shrinks pores and makes skin firm and smooth



## Treatment effect


1. Painless hair removal, no side effect.
2. Strong power, Germany imported laser diode module, 10bar, 12 bars ,16 bars available.
3. Big spot size 12\*20 mm or 12\*35 mm, for fast hair removal.
4. Best cooling system:air +water+TEC semiconductor condenser, Water temperature can be controlled between 26°C—28°C, 24 hours continuously working.



Before



After



## System

6 skin type Any language could be added

Logo could be added for free 14.0 inch touch screen

