

# Why

choose us?

## 14 years factory

14 years of focus on the development of beauty equipment, the pursuit of higher product quality, making beauty entrepreneurship easier

## 60000+ customers in 102 countries

The products are sold to 102 countries, serving more than 60,000+ customers

## 2 years warranty

2 years warranty for each machine All question will be response within 24 hours solved within 72 hours

**Make Your Beauty Business More Easier !**



## Our advantage

14 Years factory experience, A.ODM / OEM Service B.Professional R&D team and quality inspection team, after-sales and sales team C.Have CE,ISO 13485 certificate,More than 20 Patent Certificates D.The Most Mature Semiconductor Hair Removal Experience

## Products Description

**DIODE LASER**

- \*3 waves 1064nm +808nm + 755nm,
- \*Safe, Fast, Painless, permanent
- \*For all skin and hair style hair removal

>>>

- 1.Three wavelengh diode laser.
- 2.Golden laser bars from German or USA imporved□40,000,000+ longer lifespan.
- 3.Safe, Fast, Painless□permanent
- 4.For all skin and hair style hair removal

5.14.0 inch true color touch screen with 6 skin colors.

## Machine display

Show the machine from three angles, looking at the machine comprehensively.



# MACHINE DETAILS DISPLAY

EXQUISITE DETAIL DISPLAY



**About Handles**

Three Simultaneous Wavelengths in one Applicator

12mm\*20mm / 12mm\*35

4cm<sup>2</sup>

Mix Laser 755nm+808nm+1064nm  
Multiple Laser Wavelengths and Technologies

=

Alex 755nm  
Ideal for range of hair colors

Speed 808nm  
Safe for darker skin types


YAG 1064nm  
Perfect solution for darker skin



### Safety Use On All Skin Type

- 1.Alex 755nm for light skin
- 2.Speed Diode 808nm for yellow skin
- 3.Long Pulse 1064nm for darker skin





- **755nm for white skin** (fine, golden hair removal )
- **808nm for yellow neutral skin** (brown hair removal)
- **1064nm for black skin** (black hair removal)


## Product Parameters



Pulse duration	10-300ms adjustable
Crystal temperature	-27°C~5°C
Laser bar	10bar/12bar/16bar, imported from Germany/USA
Technology	Tripe waves 755+808+1064nm Technology
Output power	1000w/1200w/1600w
Laser Type	808nm diode laser or 755/808/1064nm 3 waves combined
Display system	12 inch screen
Wavelength	755/808/1064

shots	20-40 million shots
Energy	10~150 j/cm2, adjustable
Frequency	1-10HZ
Cooling	Compressor+air+water
Power	3500W
Spot size	12*20mm or 12*35mm for choose
Voltage	110V/ 60HZ or 220V/50HZ for choose
Net Weight	95Kg
Machine size	53*40*105cm

#### Screen Display



#### Machine Program

1. 14 inch big screen, quick touch
2. Male & femal, 6 body parts, 6 skin types setting smart software
3. 6 language options, your native language can be added
4. Free OEM program service(logo/system...)

Comparison chart before and after hair removal effect

