

Getting rid of unwanted hair is an age-old issue, with long-term hair removal being particularly challenging. EXFU laser hair removal method, one-stop solution for truly effective hair removal.



Advantage of 755 808 1064 Diode Laser Hair Removal Machine

- 1) Use TEC condenser, it has better cooling effect, make sure machine works continuously on 24 hours, even in summer.
- 2) Use Italy imported high pressure pump, 40,000,000 longer lifespan
- 3) 2 Filters, 1 filter for soften water, 1 filter for impurity separate.
- 4) High power 3000w, strong energy, get good hair removal effect.



360 degree bidirectional rotation



No need to drag, easily rotate various angles
Rotating without winding, the operation is more convenient




Newest Factory Lowest Price Diode Laser Hair Removal
HD 4K Screen Design

The screen can be rotated for more convenient operation

One-touch start button



Can be used for hair removal on all parts of the body, safe, painless, comfortable and permanent



Cool glow equivalent



New type EXFU diode laser hair removal machine

Painless Freezing Hair Removal



12*24mm² large cool area, no pain and no skin damage.

EXFU



755 808 1064 Diode Laser Hair Removal Handle

spot size 12*20mm, 10 bars 1000w.
spot size 12*35mm, 12 bars 1200w.
spot size 12*35mm, 16 bars 1600w.

808 Hair Removal treatment pictures



- 1) Diode laser hair removal is painless
- 2) Safe permanent hair removal on all skin types
- 3) Frozen ice cooling sapphire crystal, for painless hair removal.



Screen System

Laser Diode Machine Program

1. 14 inch big touch screen, humanized designed, diode laser operate system
2. Male/female, body parts, 6 skin types for option.
3. English+your native language.
4. Free OEM/ODM program service (logo/system...)



Product Configuration


Item	Vertical 755 808 1064nm diode laser
Laser type	Diode laser,12bars, 16bars
Power of each bar	100w
Display system	14 inch true color touch screen
Wavelength	808nm/755nm/1064nm
Spot Size	12*24mm ² /12*36mm ²
Laser handle lifespan	808nm:At least 20,000,000-40,000,000 shots
Energy	10-150 J / cm ² adjustable (up to 150J/cm ² optional)
Pulse Duration	40~800ms adjustable
Frequency	1.0-10 Hz;
Cooling system	TEC semiconductor condenser+air+close water circulation
Handle Power	1000w/1200w/1600w
Machine Power	3500w
Electrical source	220V/50HZ or 110V/60HZ

Crystal temperature	-29~5°C
Machine temperature	27°C
Power requirement	AC220V/110V 50~60Hz

Company Profile

3 years warranty

Free online training services,technical support
Big 1600w power , satisfying hair removal result



Authentication

NQA13485,CB certification
and more Complete certification
materials

60000+ Customers

We have professional after sale
team and we provide 7*24
services

2 Years Warranty

2 years warranty for each
machine, All questions will get
reponse within 24 hours

1.Weifang Mingliang Electronics Co., Ltd is a highly professional and experienced manufacturer of beauty equipment in China,has 14 years in beauty industry

2.We have professional Production R & D department,Can provide technical support□2 year warranty

ABOUT COMPANY

Shandong Xinghua Electronics Co., Ltd.



ABOUT US

[LEARN MORE](#)

14 years factory ,14 years focusing on the development of beauty equipment, Pursuit of higher product quality, Making your business easier!

All the products are taking with CE/ISO certification ,suitable for world market , mainly used on North America South America , Europe ,more than 102 countrys .





Professional
Production R&D
department



Wide range
of beauty machines



14 Years

Professional Factory



Dust-free installation
workshop



Professional
technical team

**Please consult us for more product details
24 hours online!**