




--Application of laser hair removal machine


- * High power diode laser with nice cooling technology, for hair removal with painless!
- * Suitable for any unwanted hair on areas like face, arms, armpits, chest, back, bikini, legs...
- * Frequency 1-10hz. treatment fastly!!!

Machine for fast and permanent hair removal . Painless!!






The body and screen can rotate 360° and can be pushed and pulled at will, making the use process more convenient




Exfu

NEW ARRIVAL

Style: Stationary



Available for any unwanted hair on armpits, face, neck, underarms, back, legs, bikini line.



The screen can stretch
The machine body can rotate 360°



Triple wavelength included: 755nm 808nm 1064nm

755nm suitable for light skin hair removal .
 808nm suitable for neutral skin hair removal .
 1064nm suitable for black skin hair removal .

350g lightweight handle, more ergonomic

Available in **black or white**

spot size: 12*36	spot size: 12*24	spot size: 12*36	spot size: 12*24


Suitable for any unwanted hair on areas like face, arms, armpits, chest, back, bikini, legs...


Handle of EXFU laser hair removal machine

1.12*24mm handle can you on small parts of the


body, such as face hair removal and other small place.

2.12*36mm can use at large parts of the body, such as back, arms and legs.....






Authentication
FDA,NQA13485,CB certification
and more Complete certification
materials




60000+ Customers
We have professional after sale
team and we provide 7*24
services




2 Years Warranty
2 years warranty for each
machine, All questions will get
reponse within 24 hours

The real experience is visible


Through live test verification ,safe ,long,painless
and effective




Before




After



Before



After



EXFU

Redefine hair removal equipment
OEM & ODM Professional Design

Packing

safe and thoughtful packaging service



Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable,
one-year warranty.

OEM&ODM service for distributor.

Tight packaging

Training: (Video+Manual+Online Service)
Can Keep You Operate It Easily.



3-5 business days delivery

Professional guide:
24 Hours Professional online customer service,