

360° bidirectional rotation

Rotating the machine without moving
Efficient and labor-saving



--Application of laser hair removal machine

- * High power diode laser with nice cooling technology, for hair removal with painless!
- * Suitable for any unwanted hair on areas like face, arms, armpits, chest, back, bikini, legs...
- * Frequency 1-10hz. treatment fastly!!!

Machine for fast and permanent hair removal . Painless!!

EVOLUTION OF HAIR REMOVAL

SAFE AND STABLE

3-5 SESSIONS TREATMENT

TO REMOVE HAIR PERMANENTLY

[MORE](#)

EXFU
Simple - Safe - Effective

The handle can be placed **at will**



Do as one wishes

Exfu NEW ARRIVAL

Style: Stationary



Triple wavelength included:755nm 808nm 1064nm

755nm suitable for light skin hair removal .

808nm suitable for neutral skin hair removal .

1064nm suitable for black skin hair removal .

350g lightweight handle, more ergonomic

Available in **black or white**



spot size:12*36



spot size:12*24



spot size:12*36



spot size:12*24

Suitable for any unwanted hair on areas like face,arms,armpits,chest,back,bikini,legs...



Handle of EXFU laser hair removal machine

1.12*24mm handle can you on small parts of the body, such as face hair removal and other samll place.

2.12*36mm can use at large parts of the body, such as back, arms and legs.....



Authentication

FDA,NQA13485,CB certification
and more Complete certification
materials



60000+ Customers

We have professional after sale
team and we provide 7*24
services



2 Years Warranty

2 years warranty for each
machine, All questions will get
reponse within 24 hours

Welcome to consult! 7X24 hours online service!