



Diode laser hair removal machine.

- * No pigmentation. Suitable for any kind of skin;
- * Suitable for any kind of skin ;
- * Safe and Fast.
- * International Hair Removal Golden Standard;
- * The optimal laser wavelength;
- * Long laser pulse width(10ms to 800ms);

The handle weighs only 350g! 15*20mm, 12*35mm face & body hair removal solution!

Handle display Handle color optional

weight **450g**

The handle weighs only 450g, making the treatment process easier

Cooling effect

Fast cooling, more comfortable treatment process



12*20mm



12*35mm



12*20mm



12*35mm

Cooling system:

Unique Dual- TEC cooling system,


most effective to ensure machine work all day, 24hr no down time.



Just One minute!
Quick cooling down to **-25°C**



Three Waves laser combines 755nm 808nm 1064nm, suits for all skin and hair types treatment.
755nm for white skin (fine/ golden hair) hair removal.
808nm for yellow (natural) skin hair removal.
1064nm for black skin (black hair) hair removal.



Smayer
Shandong Smayer Electronics CO.,LTD




ALEX 755nm
For white skin
 (fine, golden hair removal)




SPEED 810nm
For yellow neutral skin
 (brown hair removal)



YAG 1064nm
For black skin
 (black hair removal)



Treatment Comparison





Products Description

Laser wavelength/type	ice platinum diode laser hair removal machine price laser 755/808/1064
Power	3000W;
Laser energy output	0-150J/cm2 (adjustable)
Laser pulse width	10-800ms(adjustable);
Pulse output frequency	1-10Hz;
Spot size	12*35mm ² /12*20mm ² option
Operative LCD Interface	10.4—12 TFT True Color LCD touch screen
Cooling system	Water+air+TEC condenser
Laser bar:	10 or 12 or 16 PCS bar option
Package size:	115*59*61cm

Professional OEM ,ODM service

- A) Print any color you want for your machine, make it be you and your client favourite .
- B) Print your logo on the machine shell and add it into system as welcome interface .
Make it exclusive in the world .
- C) Add any language into machine system , according you and your client require .
- D) Add the Remote Rental System into machine to do lease business .
- E) Design exclusive machine shell for you , form your own brand in market .
- F) Design new interface and system of machine , make it most convenient to you and your clients.
- G) Develop newest technology to satisfy you and your client demand .

Certificate display

Certificate is the best guarantee for you



Packing

safe and thoughtful packaging service



Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable,
one-year warranty.

OEM&ODM service for distributor.

Tight packaging

Training: (Video+Manual+Online Service)
Can Keep You Operate It Easily.



3-5 business days delivery

Professional guide:
24 Hours Professional online customer service,