

**SAFE AND PAINLESS**

# **DIODE LASER HAIR REMOVAL MACHINE**

**LEARN MORE**



Say goodbye to unwanted hair with MLKJ's ICE laser hair removal! Our state-of-the-art technology is quick, comfortable, and effective, leaving you with smooth, soft skin that lasts. Say hello to your new, confident self today!

# 15 Years Laser Beauty Device Manuafactor

• High Feedback  
Top10 Supplier

• OEM & ODM  
SERVICE



# • *Cooling effect* •


The handle is frosted for one minute,  
making your treatment more comfortable and painless



Suitable for hair removal on any part of the body,  
Such as arms, legs, face, armpits, back, chest, etc.




- \*1800w High power diode laser with nice cooling technology, for hair removal with painless!
- \* Diode laser enable the light to penetrate deeper into skin and safer than other laser. because it can avoid the melanin pigment into the skin's epidermis, we can use it for the permanent hair removal of all color hairs on all 6 kinds skin types.
- \* Suitable for any unwanted hair on areas like face, arms, armpits, chest, back, bikini, legs...It also have the skin renewing.
- \* Frequency 1-10hz. treatment fastly!!! Machine for fast and permanent hair removal . Painless!!



755 nm for white skin (fine, golden hair removal );



808 nm for yellow neutral skin (brown hair removal);



1064 nm for black skin (black hair removal)

## Handle display

1.Three wavelengh diode laser. 2.Golden laser bars from German or USA  
imporved 40,000,000+ longer lifespan. 3.Safe, Fast, Painless permanent 4.For all skin and  
hair style hair removal 5.14.0 inch true color touch screen with 6 skin colors.



24 hours work  
Keep the effect

**Waves laser combines 755nm 808nm 1064nm, suits for all skin and hair types treatment.**

755nm for white skin (fine/ golden hair) hair removal.

808nm for yellow (natural) skin hair removal.

1064nm for black skin (black hair) hair removal.

# For all skin types

**Triple wavelength** laser work together

755  
nm

808  
nm

1064  
nm

755nm/808nm/1064nm

755nm  
808nm  
1064nm

## Laser hair removal treatment theory



Hair active growth phase(3-6years)



laser treatment



Transition phase (1-2weeks)



Resting phase (1-2 weeks)



Return to growth phase

Model	808V29
Laser Type	808nm diode laser or 755/808/1064nm 3 waves combined
Display	14 inch 4K touchable screen
Wavelength	755/808/1064
shots	20-40 million shots
Energy	10~150 j/cm2, adjustable
Frequency	1-10HZ
Cooling	Compressor+air+water
Power	3500W
Spot size	12*24mm or 12*36mm for choose
Voltage	110V/ 60HZ or 220V/50HZ for choose
Net Weight	95Kg
Gross Weight	105Kg
Machine size	53*40*105cm

Box size

125\*56\*70.4



Painless 810nm-755nm *V2.9*  
Diode laser handle  
Suitable for all skin tones and body parts

**Painless hair removal, no side effect□Make your skin silky and full of charm!**

**Screen system display**

**Operation System**

- \* 14.0 inch screen
- \* multi-language system
- \* Easy to operateproviding operation skills and teaching services

\*Free logo and language can be customized

## Custom Section

### LOGO design



### SYSTEM design



Custom section

You can customize your exclusive logo screen according to your needs



# Our customers

60000+ CUSTOMERS



102

Countries

OEM/ODM

Customize the machine according to customer needs

CERTIFICATE



14 years manufacturer with rich experience in producing beauty machines!

13 years Alibaba golden supplier

CE certificates approved TUVcertificates approved

Personal custom made & OEM

## Product packaging

The aluminum box packaging machine is sturdy and durable, with safety protection, helping your machine get home safely!

# Packing

safe and thoughtful packaging service



## Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable,  
one-year warranty.

**OEM&ODM service for distributor.**

## Tight packaging

Training: (Video+Manual+Online Service)  
Can Keep You Operate It Easily.



## 3-5 business days delivery

Professional guide:

24 Hours Professional online customer service,