

 **Smayer**

**A new  
winner  
is born!**



**2021 WINNER  
EUROPEAN  
PRODUCT  
DESIGN  
AWARD**

**V28: Diode Laser hair removal machine**

- 1) Stronger, Faster, SmarterHair removal
- 2) New 3D technology 755nm 810nm 1064nm
- 3) Stronger 800/1000/1200/1600watt, 40% faster



### **Why all beauty salons, beauticians prefer 808nm diode Laser hair removal machine ?**

- A) Safer, no side effects on skin and sweat glands, no scar.
- B) 755nm+808nm+1064nm suitable for all skin types, black skin and fine hair can be easily treated, suitable to all types.
- C) Long laser width, high energy, effective for the hair follicles produce heat accumulation, Permanent hair removal.
- D) Quick! Big spot size 12\*35mm could prompt the treatment speed, treatment speed and efficiency.
- E) Strong cooling system can make momentary epidermal anesthesia, no any painless during.

### **About Handles**




### Ice titanium 808nm diode laser hair removal machine

Large 12\*20mm/12\*35mm spot size for quick treatment

I-VI skin types and tanned skin safe and painless permanent hair removal

### Laser show Handle laser bar optional





Most important thing 3 wavelengths 755+808+1064 covering the optimal treatment painless proven safety permanent hair removal

For all skin types

ICE PLUS continuous cooling system. The treatment process is more comfortable.


It can work continuously for 24 hours.



**Just One minute!** Quick cooling down to **-25°C**



# Treatment Comparison



## Screen Display Machine Program

1. 14 inch big screen, quick touch
2. Male & female, 6 body parts, 6 skin types setting smart software
3. 6 language options, your native language can be added
4. Free OEM program service( language/logo/system/color...)

# FREE LOGO SERVICE







# 14 Years Laser Beauty Decvice Manuafactor

- High Feedback **Top10 Supplier**
- **OEM & ODM SERVICE**



R & D design Design and development teams from the United States and Germany.  
 Certified and tested mature production line and quality inspection team and standard production line.  
 What we care about most is High-quality products are the standard for maintaining cooperation.

## Certificate display

Certificate is the best guarantee for you



**Product Paramenters**



Model	Diode Laser V28
Laser Type	Germany/USA imported, 10bars,12 bars, 16 bars
Display	14---15.6 inch 4K touchable screen
Wavelength	755nm 808nm 1064nm
Shots	40 million shots
Energy	10~150 j/cm2, adjustable
Frequency	1-10HZ
Cooling	TEC+Air+Water Cooling
Power	3500W
Spot size	12*20mm/12*35mm for choose
Voltage	110V/ 60HZ or 220V/50HZ for choose
Net Weight	95Kg
Gross Weight	105Kg
Machine size	45*52*110cm
Box size	56*70.4*125cm
Delivery time: 3-7 working days after payment	
Delivery way: by air, DHL , TNT , Fedex, or delivery agent	
Before delivery: testing video and pictures	
After delivery Warranty: 2 years,offer impeccable after-sale service	

## **Packing And Shipping**



# Packing

Safe and thoughtful packaging service



## Tight packaging

The machine shall be made of waterproof materials and packaged

**Anti collision foam board  
inside aluminum box**



## 3-5 business days delivery

Professional guide:

24 Hours Professional online customer service

# CONTACT US



## In terms of following trade details:

- 1)The shipping cost are based on DHL cost to your country
- 2)Delivery time:3-5 days after receiving payments.
- 3)Payment terms:T/T(bank transfer),Western Union.
- 4)Warranty:2 years for the whole machine
- 5)Warranty Policy:one month guarantee replacement (we bear all shipping cost),2years warranty,lifelong maintenance.
- 6)Packing method: Aluminum box with hard plastic foam.
- 7)Free-training to customers:Free We could offer DVD and User's manual and 10 Hours online service to our customers
- 8)Certifications:CE TUV SFDA ISO 13485
- 9)MOQ:1 UNIT
- 10)The quotation here above is valid within 1 month