

Already help over customers from 102 countries make good business.


Various templates for you to choose.

### **Product Description**




### **Advantages**


1. 3 waves Yag 1064nm + Diode 808nm + Alex 755nm, 3 in 1 all skin type can be used  
High power: NEW 1000W/ 1200W /1600W handle for options
2. Big spot size 15\*25mm, 12\*20mm, 12\*38mm, face & body hair removal solution!
3. Cooling system: Unique Dual- TEC cooling system, most effective to ensure machine work all day, 24hr no down time.
4. Long life: double life support guarantee



**A** natural



**B** energy absorbed by hair



**C** hair follicle died

**Safe Use On All Skin Type**

Alex 755nm for light skin

Speed Diode 808nm for yellow skin

Long Pulse 1064nm for darker skin

# Handle Details

Three Wavelengths Work Togher





## Features & Diode Laser

1. Laser bar: Imported laser bar US Coherent/ Dilas brand
  2. 3 waves: 755nm 808nm 1064nm 3 in 1
  3. Spot size: 12\*20mm, 12\*35mm
  4. Power: High power 1000W 1200W 1600W & OEM
3. Cooling: Super cooling start frozen in 1 minutes, 24 hr continue work

## Software & Program

1. Easy Start: Based on male & femal/6 body parts, Add 6 skin types setting smart software
2. 6 language options, your native language can be added
3. OEM program service available(logo/system...)





**For more model details, please contact us!**  
**Online 24 hours!!**