



D10

Portable Hair Removal Machine

Three bands: 755nm/808nm/1064nm
Suitable for all skin types



DIODE LASER hair removal machine

■ 2 Years Warranty ■ OEM / ODM Service ■ 3 waves 1064nm + 808nm + 755nm

About hair removal machine D10

- * USA or Germany imported laser bar 8—12bar.
- * More than 50 million shots , more than 3 years don't need to change new handle.
- * 3 waves 1064nm + 808nm + 755nm, 3 in 1 all skin type can be used

Handle Display

Two colors, two spot sizes are optional



Triple wavelength included:755nm 808nm 1064nm

755nm suitable for light skin hair removal .

808nm suitable for neutral skin hair removal .

1064nm suitable for black skin hair removal .

Working Principle

755nm and 808nm and 1064nm , suits for all skin and hair types.



ALEX 755nm

For white skin

(fine, golden hair removal)



SPEED 810nm

For yellow neutral skin

(brown hair removal)



YAG 1064nm

For black skin

(black hair removal)

The real experience is visible

Through live test verification ,safe ,long,painless
and effective



- 1) Big size: used 14 inch color touch screen.
- 2) Multiple language: three kinds of skin types option,easy to operate.
- 3) OEM service: your logo can be added on machine screen for free,accept your special language.



Product details

Ultra-thin large screen, cool light strip



**For more details, please consult us!
24 hours online!**