

OEM / ODM Service
Any style , any color you wanted

Build more trusted partners

Our customers

60000+ CUSTOMERS


OEM/ODM

Customize the machine according
to customer needs



CERTIFICATE

Obtained multi-way authoritative certification,
product testing certification, product patent authority,



Advantages

- * USA or Germany Dilas imported laser bar.
- * More than 40 million shots , more than 3 years don't need to change new handle.
- * 808nm All skin type can be used
- * High power: NEW 1200W /1800W handle for options
- * Medical handle spot size 12*24mm Or 12*36mm, face & body hair removal solution!
- * Cooling system: Unique Dual- TEC cooling system, most effective to ensure machine work all day, 24hr no down time.
- * Long life: 40 million shots

Handle Display

12*24mm or 12*36mm handle

Suitable for any unwanted hair on areas
like face, arms, armpits, chest, back, bikini, legs...



1200w ,1800w big power for free choice

12*24 or 12*36 mm spot size

*350g Medical handle, light weight, free quick slide treatment

* With indicator light, to show working condition(on machine & handle), safely use



cooling


- * turn on machine, immediately cooling , immediately hair removal
- * good cooling longer handle lifespan
- * real ice painless hair removal effect

Treatment Effect

Hair removal comparison

The real picture taken by the customer

Different parts of men and women, as well as different skin colors can have very good hair removal results, they all get a permanent and painless hair removal experience



Before



After Treatment

Hair removal comparison

The real picture taken by the customer

Different parts of men and women, as well as different skin colors can have very good hair removal results, they all get a permanent and painless hair removal experience



Before



After Treatment

Machine Program

1. 14 inch big screen, quick touch
2. Male & female, 6 body parts, 6 skin types setting smart software
3. 6 language options, your native language can be added
4. Free OEM program service (logo/system...)

5.OEM / ODM Service

- >>OEM your own machine body
- >>OEM your own program software
- >>OEM pretty machine colors
- >>Print your LOGO on machine body and screen
- >>R & D team and Quality inspection Show

6.Certificate Display

R & D design Design and development teams from the United States and Germany. Standard production line. Certified and tested mature production line and quality inspection team. What we care about most is High-quality products are the standard for maintaining cooperation.

Product Parameters

Model	808V19
Laser Type	Germany/USA imported, 12 bars, 18 bars
Display	14 inch 4K touchable screen
Wavelength	808mm or 755mm 808mm 1064mm
shots	20-40 million shots
Energy	10~150 j/cm ² , adjustable
Frequency	1-10HZ
Cooling	High Speed Double TEC coolingAir and Close Water Circulation Treatment head with semiconductor cooling temperature adjustable
Power	3500W
Spot size	12*24mm or 12*36mm for choose
Voltage	110V/ 60HZ or 220V/50HZ for choose
Net Weight	95Kg

Gross Weight 105Kg
Machine size 53*40*105cm
Box size 125*56*70.4

Product packaging

Delivery time 3-7 working days after payment
Delivery way by air, DHL , TNT , Fedex, or delivery agent
Before delivery testing video and pictures
After delivery Warranty: 2 years,offer impeccable after-sale service
Package Aluminum Box with Foam inside ,and Wheels Outside

Packing

safe and thoughtful packaging seivice



Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable,
one-year warranty.

OEM&ODM service for distributor.

Tight packaging

Training: (Video+Manual+Online Service)
Can Keep You Operate It Easily.



3-5 business days delivery

Professional guide:
24 Hours Professional online customer service,