



2021 Salon Queen

FASTER: 60% FASTER
 STRONGER: STRONGER POWER 40%
 BETTER RESULT
 SMARTER: 4K ANDROID SCREEN

FASTER, STRONGER, SMARTER

1. Three wavelength diode laser.
2. Golden laser bars from German or USA improved 40,000,000+ longer lifespan.
3. Safe, Fast, Painless, permanent
4. For all skin and hair style hair removal
5. 14.0 inch true color touch screen with 6 skin colors.
6. Two models can be selected, single handle or double handle



V26

Super comfortable experience
 Painless and permanent treatment result
 Suitable for all skin types and body areas

Most advanced TEC cooling system inside this machine to deliver a super good cooling results.
24 hours working time.Sapphire material.Actual Pain-free experience!


- 1)10 bars/ 12 bars/ 16 bars, 10-40 million shots.
- 2)Big spot 12*20mm / 12*35mm for fast hair removal.
- 3)Frozen ice cooling sapphire crystal, for painless hair removal.
- 4)Hight quality gold laser bar imporved from German.
- 5)Medical handle as low as 350g easy to treatment.

Screen system

1. 14 inch big touch screen, humanized designed.
2. Male/femal, body parts, 6 skin types for option.
3. 6 language systems, native language + whatever you want.
4. Free OEM program service(logo/system...)

Laser bar	Germany/USA imported, 8 bar, 10 bar, 12 bars, 16 bars
Wavelength	755nm 808nm 1064nm/ or single 808nm
Energy	0-150J/cm2
Frequency	1-10hz
Pulse width	40-800ms
Operative LCD Interface	14.0 TFT True Color LCD touch screen
Cooling system	Air and Close Water Circuitation Treatment head with semiconductor cooling temperature adjustable
Power	4000W
Electrical source	220V/50HZ or 110V/60HZ
N.W/ G.W	62kg/78kg


Company Strength



- >>OEM your own machine body.
- >>OEM your own program software.
- >>OEM pretty machine colors.
- >>Print your LOGO on machine body and screen.

Custom Section


CASE design



LOGO design



SYSTEM design




Certificate Display

CERTIFICATE DISPLAY



Packing

safe and thoughtful packaging service



Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable,
one-year warranty.

OEM&ODM service for distributor.

Tight packaging

Training: (Video+Manual+Online Service)
Can Keep You Operate It Easily.



3-5 business days delivery

Professional guide:
24 Hours Professional online customer service,