



MLKJ cost-effective 4in1 multifunction laser beauty machine diode Laser+ipl laser+nd yag laser+rf laser



The newest 4-in-1 multifunction laser beauty machine combines four different laser technologies: diode laser, IPL laser, ND:YAG laser, and RF laser. Each technology has its own application fields and advantages, which are summarized below:

Real shot display



808 handle



Elight handle



ND YAG Laser handle



RF handle



Diode Laser:

Application Fields:

Hair Removal: Diode lasers are highly effective for permanent hair reduction on various skin types. Advantages: Precision: Diode lasers can target specific areas, ensuring precise hair removal. Speed: Diode lasers have larger spot sizes and high repetition rates, enabling quick treatment sessions. Safety: They offer selective photothermolysis, minimizing damage to the surrounding skin.

DIODE LASER

755/808/1064nm diode laser, for all type skin hair removal, painless



ADVANTAGE

- **PAINLESS:** 755/808/1064nm diode laser for all type skin hair removal
- **FASTER:** Large area spot sliding operation
- **NO TRAUMA:** There is no trauma to skin tissue
- **SAFETY:** To avoid the light of the deputy to reduce the difficulty of operation



Suitable for hair removal on any part of the body,
Such as arms, legs, face, armpits, back, chest, etc.



• *Cooling effect* •

The handle is frosted for one minute,
making your treatment more comfortable and painless



IPL (Intense Pulsed Light) Laser:

Photorejuvenation: IPL can improve the appearance of sun-damaged skin, age spots, freckles, and vascular lesions. Hair Removal: IPL can target melanin in hair follicles for effective hair reduction. Advantages: Versatility: IPL can address a range of skin concerns, including pigmentation issues and vascular lesions. Non-invasive: IPL treatments are generally non-invasive and have minimal downtime.

Elight handle



specification

- High-quality: Elight handpiece with super cooling system
- Optional Spot Size 15*50mm
- Long shots time: 150000 times
- 7 filters: 420/510/560/585/640/690/755nm
Standard: 420/510/680nm



Before & After



Hair removal



Skin rejuvenation



Freckle removal



Acne removal



Vascular



Skin firming

ND:YAG Laser:

Application Fields:

Tattoo Removal: ND:YAG lasers can effectively remove various types and colors of tattoos.

Pigmented Lesion Treatment: They can target and reduce the appearance of pigmented lesions like birthmarks and age spots.

Advantages:

Versatility: ND:YAG lasers can target a wide range of pigments, making them suitable for different tattoo and pigmentation types.

Safety: They have a longer wavelength, which can penetrate deeper into the skin, minimizing damage to the surface.

HANDLE-ADVANTAGE



specification

- **Multiple choice**
fixed 1064nm & 532nm, adjustable 1064nm & 532nm (adjust 1-7 mm) for tattoo removal, nevus removal etc.
- **Multifunction**
1320nm for skin rejuvenation
- **Indicator light**
Dot position is the indicator light position dot more accurate



Adjustable
532nm



Adjustable
1064nm



Black doll
1320nm



Fixed
532nm



Fixed
1064nm



Before&after compare



before



One cycle



Two cycles



Three cycles

Tattoo removal



Tattoo removal



Nevus of Ota removal



Tattoo on brow removal



Lioline removal



Lioline removal



Tattoo on brow removal



RF (Radiofrequency) Laser:

Application Fields:

Skin Tightening: RF lasers can stimulate collagen production, leading to skin tightening and wrinkle reduction.

Advantages:

Non-surgical: RF lasers provide a non-surgical option for achieving skin tightening and rejuvenation.

Minimal Downtime: They typically have little to no downtime, allowing patients to resume regular activities quickly.



Skin rejuvenation/Vascular/Acne



before



after



before



after



before



after

BEFORE & AFTER [®]



Hair removal



Skin rejuvenation



Freckle removal



Acne removal



Vascular



Lose weight

SCREEN INTERFAC [®]

Professional Screen, Easy operation



Screen size	14 inch true color touch screen
Pulse Duration	10-300ms
Frequency	1-10hz
Spot size	Elight: 15*50mm Diode laser: 12*20mm&12*35mm
Energy	1-150J/cm2
Cooling	Water cooling+Air cooling+TEC condenser cooling system

Voltage	AC220V/110V 50HZ/60HZ
Demension of machine	113*65*76cm
Package	Aluminum box
Warranty	2 years

The 4-in-1 multifunction laser beauty machine offers the advantage of versatility, allowing practitioners to address multiple aesthetic concerns using a single device. It provides a comprehensive range of treatments, including hair removal, photorejuvenation, tattoo removal, pigmented lesion treatment, and skin tightening.





Authentication

CE,NQA13485,CB certification
and more Complete certification
materials



60000+ Customers

We have professional after sale
team and we provide 7*24
services



2 Years Warranty

2 years warranty for each
machine, All questions will get
reponse within 24 hours

CERTIFICATE DISPLAY



Packing

safe and thoughtful packaging service



Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable,
one-year warranty.

OEM&ODM service for distributor.

Tight packaging

Training: (Video+Manual+Online Service)
Can Keep You Operate It Easily.



3-5 business days delivery

Professional guide:
24 Hours Professional online customer service,

1. Is it a reliable company?

Weifang Mingliang Development Co., Ltd. Is established in 2005, engaged in R&D, sales and after-sales services of aesthetic devices & medical laser equipments, even part of IT area and Real estate sector. We have a professional team integrating with optics, machinery, electricity and medicine, to keep us ahead on in this field. factory covers 5000M2 and has more than 100 employees.

2: What about the delivery?

We can offer the door to door services by air or by sea, just depend on your actual request. Such as DHL, UPS, TNT, FEDEX... by air; and the sea transportations.

3: What's the delivery time?

3-5 working days. Huge stock.

4: What's package?

Strong and beautiful aluminum alloy case/carton case/wooden case.

5: Do you have any timely technology supports?

We have a professional technology supporting team for your timely services. We prepare the technical documents for you, also you can contact us by telephone, webcam, online chat (googletalk, MSN, skype, yahoo...).

6: What's the payment method?

T/T, WESTERN UNION, ESCROW and etc.

7: If the machines broken during the shipment, will you support us?

Generally our customer will purchase the insurance before shipment, avoid any money lost from rough transportation. We will help you to solve the claims with the insurance companies to collect your money back in time.

Beauty instrument factory, beauty salon, beauty instrument OEM, beauty instrument customization

**If you have any questions□please feel free to contact me.
Your prompt reply will be highly appreciated.**