

# Medical handle is Lighter handle

## Stronger, Faster, Smarter

1600w big handle power   24 hours working   Painless hair removal



● 12\*24mm<sup>2</sup>



● 12\*36mm<sup>2</sup>

[Learn more](#)



Best Selling

14 years factory, 2 years warranty, 102 countries, 60,000+ customers

MLKJ——Make Your Beauty Business More Easier

## Machine advantage:

- Machine warranty 2 years
- Custom language system
- 1800w high power hair removal
- Fast and safe



### Advantages

1.3 waves 1064nm + Diode 808nm + 755nm, 3 in 1 all skin type can be used

High power: NEW 1200W /1800W handle for options

2.Big spot size 12\*24mm, 12\*36mmface & body hair removal solution!

3.Cooling system: Unique Dual- TEC cooling system, most effective to ensure machine work all day, 24hr no down time.


4.Long life: double life support guarantee

# TEC cooling system

One minute cooling -21°C

Best **TEC Cooling** system  
hair remover laser





### **Features of Platinum Diode laser hair removal:**

- »»Safety:No skin scald, no harm to the skin and sweat glands, no scar, no any side-effect.
- »»Quick: big spot size 12\*36mm, effective and quick treatment on big treatment area
- »»Permanent hair removal: remove all hair on all skin types, including tanned skin.
- »»Crystal temperature: ~5-3°C, reduce the painful and increase comfortable sense in treatment.

### **Handle Details**

# Hair removal principle

Make Your Beauty Business More Easier




The laser selectively acts on the melanin in the hair follicle, destroying the hair-growing area

Natural hair loss, prevent regeneration, and achieve the purpose of hair removal

Hair removal also stimulates collagen regeneration, shrinks pores and makes skin firm and smooth








755 nm for white skin (fine, golden hair removal );



808 nm for yellow neutral skin (brown hair removal);



1064 nm for black skin (black hair removal)

## Handle Long life time 20-40 millions shots

Suitable for diode laser hair removal on all skin of the body

Laser Type	808nm diode laser or 755/808/1064 3 wave
Display	14 inch touch screen system
Wavelength	808nm or 755/808/1064nm
shots	40 million shots
Energy	10~150 j/cm <sup>2</sup> , adjustable
Frequency	1-10HZ
Cooling	Double TEC cooling
Power	3000W
Spot size	12*36mm or 12*24mm for choose
Voltage	110V/ 60HZ or 220V/50HZ for choose

1)Screen can add your own logo

2)screen with 6 languages

3)different body parts for choose, one touch can start your treatment!


# Certificate display

Certificate is the best guarantee for you



# Packing

safe and thoughtful packaging service



## Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable,  
one-year warranty.

**OEM&ODM service for distributor.**

## Tight packaging

Training: (Video+Manual+Online Service)  
Can Keep You Operate It Easily.



## 3-5 business days delivery

Professional guide:  
24 Hours Professional online customer service,

### Company Profile

1. Weifang Mingliang company has 14 years of beauty equipment manufacturing experience



# Customer visit



2.We have professional Production R & D department

3.Feedback from customers□Support machine shell OEM □Machine system OEM□can add your own logo....