

14 years manufacturer
with rich experience in producing beauty machines!

- * Spot size 12*24mm, 12*36mm, for option
- * Medical handle, light weight, free quick slide treatment
- * can selected Parameters for different skin tones
- * 3in1 handle, Alex755nm + speed808nm + yag1064nm, multiple laser wavelengths and technologies

[LEARN MORE](#)

Advantages

- * USA or Germany Dilas imported laser bar.
- * More than 40 million shots , more than 3 years don't need to change new handle.
- * 3 waves 1064nm +808nm + 755nm, 3 in 1 all skin type can be used
- * High power: NEW 1000W/ 1200W /1600W handle for options
- * Medical handle spot size 12*24mm, 12*36mm, face & body hair removal solution!
- * Cooling system: Unique Dual- TEC cooling system, most effective to ensure machine work all day, 24hr no down time.
- * Long life: 40 million shots

1.Handle Display

1200w ,1800w big power for free choice

12*24 or 12*36 mm spot size

- *350g Medical handle, light weight, free quick slide treatment
- * With indicator light, to show working condition(on machine & handle), safely use



2.Cooling

- * turn on machine, immediately cooling , immediately hair removal
- * good cooling longer handle lifespan
- * real ice painless hair removal effect


12*24mm or 12*36mm handle

Suitable for any unwanted hair on areas like face, arms, armpits, chest, back, bikini, legs...



3.Safety Use On All Skin Type

- 1.Alex 755nm for light skin
- 2.Speed Diode 808nm for yellow skin
- 3.Long Pulse 1064nm for darker skin



More powerful energy absorption by the melanin chromophore, making it odeal for the widest range of hair types and color
 - especially light-colored and thin hair

Deep penetration of the hair follicle with high average power with high repetition rate for fast treatment. moderate melanin absorption level making it safe for darker skin types.
 ideal for treating the arms, legs, cheeks and beard.

low melanin absorption, focused solution for darker skin types. Offers the deepest penetration of the hair follicle, embedded hair in areas as the scalp, armpit, and pubic area.

Hair removal comparison

The real picture taken by the customer

Different parts of men and women, as well as different skin colors can have very good hair removal results, they all get a permanent and painless hair removal experience



Before



After Treatment

Hair removal comparison

The real picture taken by the customer

Different parts of men and women, as well as different skin colors can have very good hair removal results, they all get a permanent and painless hair removal experience



Before



After Treatment

4. Machine Program

1. 14 inch big screen, quick touch
2. Male & femal, 6 body parts, 6 skin types setting smart software
3. 6 language options, your native language can be added
4. Free OEM program service(logo/system...)

5. OEM / ODM Service

- >>OEM your own machine body
- >>OEM your own program software
- >>OEM pretty machine colors
- >>Print your LOGO on machine body and screen
- >>R & D team and Quality inspection Show

6. Certificate Display

Build more trusted partners

Our customers

60000+ CUSTOMERS

OEM/ODM

Customize the machine according to customer needs



CERTIFICATE

Obtained multi-way authoritative certification,
product testing certification, product patent authority,



7.Product packaging

Delivery time	3-7 working days after payment
Delivery way	by air, DHL , TNT , Fedex, or delivery agent
Before delivery	testing video and pictures
After delivery	Warranty: 2 years,offer impeccable after-sale service
Package	Aluminum Box with Foam inside ,and Wheels Outside

For more details, please contact us!
24 hours online!!