

Advantages

1.3waves



Large Spot Size

Quick and Comfortable

With large spot size of $1.2 \times 3.5 \text{cm}^2$, for faster treatments and better patient experience.



TEC Plus

Continuous Contact Cooling

TEC is an advanced technology that continuously cools skin and facilitates range-controlled temperature throughout the entire treatment. Patients can now enjoy a completely pain-free, cool and comfortable experience throughout the session.

Handle

- * Imported gold laser bar, Shots up to 40 million
- * 10bar **1000W**, 12 bar **1200W** and 16 bar **1600W** high power options* Spot size 12*20mm, 15*25mm, 12*38mm for option
- * 450g handle, light weight, free quick slide treatment
- * With indicator light, to show working condition(on machine & handle), safely use


Handle Details

Three Wavelengths Work Togher




12*20nm

755nm Laser
808nm Laser
1064nm Laser



12*35nm

755nm Laser
808nm Laser
1064nm Laser



Safe Use On All Skin Type

Alex 755nm for light skin


Speed Diode 808nm for yellow skin

Long Pulse 1064nm for darker skin

Working Principle


Triple wavelength laser work together

Suits for all skin and hair types



- **755nm for white skin** (fine, golden hair removal)
- **808nm for yellow neutral skin** (brown hair removal)
- **1064nm for black skin** (black hair removal)

Treatment effect





Machine Program

1. 12.4 inch big screen, quick touch
2. Male & femal, 6 body parts, 6 skin types setting smart software
3. 6 language options, your native language can be added
4. Free OEM program service(logo/system...)

L
a
s
e
r
l
i
c
e
a
h
a
i
r
r
e
m
o
v
a
l
m
a
c
h
i
n
e

G
e
r
m
a
n
y
/
U
S
A
i
m
p
o
r
t
e
d
,
8
b
a
r
,
1
b
a
r
,
1
2
b
a
r
s
,
1
6
b
a
r
s

7/55 nm 88 nm 164 nm
1W + 16W
ower &