

Advantages

1.3waves



Large Spot Size

Quick and Comfortable

With large spot size of $1.2 \times 3.5 \text{cm}^2$, for faster treatments and better patient experience.



TEC Plus

Continuous Contact Cooling

TEC is an advanced technology that continuously cools skin and facilitates range-controlled temperature throughout the entire treatment. Patients can now enjoy a completely pain-free, cool and comfortable experience throughout the session.

Handle

- * Imported gold laser bar, Shots up to 40 million
- * 10bar **1000W**, 12 bar **1200W** and 16 bar **1600W** high power options* Spot size 12*20mm, 15*25mm, 12*38mm for option
- * 450g handle, light weight, free quick slide treatment
- * With indicator light, to show working condition(on machine & handle), safely use


Handle Details

Three Wavelengths Work Togher




12*20nm

755nm Laser
808nm Laser
1064nm Laser



12*35nm

755nm Laser
808nm Laser
1064nm Laser



Safe Use On All Skin Type

Alex 755nm for **light skin**


Speed Diode 808nm for **yellow skin**

Long Pulse 1064nm for **darker skin**

Working Principle


Triple wavelength laser work together

Suits for all skin and hair types



- **755nm for white skin** (fine, golden hair removal)
- **808nm for yellow neutral skin** (brown hair removal)
- **1064nm for black skin** (black hair removal)

Treatment effect





Machine Program

1. 12.4 inch big screen, quick touch
2. Male & femal, 6 body parts, 6 skin types setting smart software
3. 6 language options, your native language can be added
4. Free OEM program service(logo/system...)

E
a
s
e
n
t
i
c
e
a
h
a
i
r
r
e
m
o
v
a
l
m
a
c
h
i
n
e

G
e
r
m
a
n
y
/
U
S
A
i
m
p
o
r
t
e
d
,
8
b
a
r
,
1
b
a
r
,
1
2
b
a
r
s
,
1
6
b
a
r
s

7
5
5
n
m
8
8
n
m
1
6
4
n
m

1
W
+
1
6
W
o
w
e
r
&