

4 in 1





Products Description

Real shot display



808 handle



Elight handle



ND YAG Laser handle



RF handle



Diode laser+Elight/IPL+Nd yag+RF, 4 different handles into one machine

This 4 in 1 RF+Elight IPL+diode laser+nd yag laser have high quality accessories , strong power

*Diode laser handle use Germanyimported golden laser bar ,50 million shots time.

*Elight handle use UK lamp, 150,000-30,000shots

*Nd yag :Equip 5 treatment heads, adjustable 1064nm/532nm, fixed 1064nm/532nm, fixed 1320nm.

*RF :Equip 6 treatment heads, used for wrinkle removal, skin lifting, skn tightening.

DIODE LASER

755/808/1064nm diode laser, for all type skin hair removal, painless



ADVANTAGE

- **PAINLESS:** 755/808/1064nm diode laser for all type skin hair removal
- **FASTER:** Large area spot sliding operation
- **NO TRAUMA:** There is no trauma to skin tissue
- **SAFETY:** To avoid the light of the deputy to reduce the difficulty of operation



Suitable for hair removal on any part of the body,
Such as arms, legs, face, armpits, back, chest, etc.



• *Cooling effect* •

The handle is frosted for one minute,
making your treatment more comfortable and painless



Elight handle



specification

- High-quality: Elight handpiece with super cooling system
- Optional Spot Size 15*50mm
- Long shots time: 150000 times
- 7 filters: 420/510/560/585/640/690/755nm
Standard: 420/510/680nm



HANDLE-ADVANTAGE



specification

- **Multiple choice**
fixed 1064nm & 532nm, adjustable 1064nm & 532nm (adjust 1-7 mm) for tattoo removal, nevus removal etc.
- **Multifunction**
1320nm for skin rejuvenation
- **Indicator light**
Dot position is the indicator light position dot more accurate



Adjustable
532nm



Adjustable
1064nm



Black doll
1320nm



Fixed
532nm



Fixed
1064nm



Before&after compare



before



One cycle



Two cycles



Three cycles

Tattoo removal



Tattoo removal



Nevus of Ota removal



Tattoo on brow removal



Lioline removal



Lioline removal



Tattoo on brow removal



RF Handl^e



12mm
eye-rf

28mm small
tripolar rf head

36mm big
tripolar rf head

14mm
bipolar-rf

28mm
bipolar-rf

38mm
bipolar-rf

Skin rejuvenation/Vascular/Acne



before



after



before



after



before



after

BEFORE & AFTER [®]



Hair removal



Skin rejuvenation



Freckle removal



Acne removal



Vascular



Lose weight

SCREEN INTERFAC [®]

Professional Screen, Easy operation



Screen size	14 inch true color touch screen
Pulse Duration	10-300ms
Frequency	1-10hz
Spot size	Elight: 15*50mm Diode laser: 12*20mm&12*35mm
Energy	1-150J/cm2
Cooling	Water cooling+Air cooling+TEC condenser cooling system

Voltage	AC220V/110V 50HZ/60HZ
Demension of machine	113*65*76cm
Package	Aluminum box
Warranty	2 years

Company Profile





Authentication

CE, NQA13485, CB certification
and more Complete certification
materials



60000+ Customers

We have professional after sale
team and we provide 7*24
services



2 Years Warranty

2 years warranty for each
machine, All questions will get
reponse within 24 hours

Certifications

CERTIFICATE DISPLAY



Product packaging

Packing

safe and thoughtful packaging service



Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable,
one-year warranty.

OEM&ODM service for distributor.

Tight packaging

Training: (Video+Manual+Online Service)
Can Keep You Operate It Easily.



3-5 business days delivery

Professional guide:
24 Hours Professional online customer service,

FAQ

1. Is it a reliable company?

Weifang Mingliang Development Co., Ltd. Is established in 2005, engaged in R&D, sales and after-sales services of aesthetic devices & medical laser equipments, even part of IT area and Real estate sector. We have a professional team integrating with optics, machinery, electricity and medicine, to keep us ahead on in this field. factory covers 5000M2 and has more than 100 employees.

2: What about the delivery?

We can offer the door to door services by air or by sea, just depend on your actual request. Such as DHL, UPS, TNT, FEDEX... by air; and the sea transportations.

3: What's the delivery time?

3-5 working days. Huge stock.

4: What's package?

Strong and beautiful aluminum alloy case/carton case/wooden case.

5: Do you have any timely technology supports?

We have a professional technology supporting team for your timely services. We prepare the technical documents for you, also you can contact us by telephone, webcam, online chat (googletalk, MSN, skype, yahoo...).

6: What's the payment method?

T/T, WESTERN UNION, ESCROW and etc.

7: If the machines broken during the shipment, will you support us?

Generally our customer will purchase the insurance before shipment, avoid any money lost from rough transportation. We will help you to solve the claims with the insurance companies to collect your money back in time.