



New arrivals

EXFU

SIMPLE . SAFE . ENJOY
New experience of hair removal



On sale! FDA approved medical painless and permanent clinical hair removal treatment machine

Advantages

- * USA or Germany imported laser bar 10bars/15bars
- * More than 50 million shots , more than 3 years don't need to change new handle.
- * 3 waves 1064nm +808nm + 755nm, 3 in 1 all skin type can be used



EXFU VIOLIN Portable Hair Removal Laser



Simple • Safe • Enjoy
Redefine hair removal equipment



one-button start



Ice hair removal



super power



40million shine

Products Description

Ingenious details I am better than others

Product detail
layout



Surround light strip

Cool lighting effect
not dazzling



Newest design handle 0.31kg

One minute cooling
Customizable glowing logo



One-of-a-kind styling

Ingenious production
focus on details



About Handle

1200W/1800W big power for free choice

12*24 or 12*36mm spot size

*285g Medical handle, light weight, free quick slide treatment

* With indicator light, to show working condition(on machine & handle), safely use

1 minute quick frosting, comfortable and painless treatment experience



Two colors, two spot sizes are optional



Suitable for any unwanted hair on areas like face, arms, armpits, chest, back, bikini, legs...

755+808+1064nm, suitable for permanent hair removal of all skin types




ALEX 755nm
For white skin
(fine, golden hair removal)



SPEED 810nm
For yellow neutral skin
(brown hair removal)



YAG 1064nm
For black skin
(black hair removal)



Model

Exfu diode laser

Laser Type	Germany/USA imported, 8---12bars, 800W---1200W
Display	14 inch 4K touchable screen
Wavelength	808nm or 755nm 808nm 1064nm
shots	50 million shots
Energy	10~150 j/cm2, adjustable
Frequency	1-10HZ
Cooling	High Speed Double TEC coolingAir and Close Water Circulation Treatment head with semiconductor cooling temperature adjustable
Power	3500W
Spot size	12*24mm or 12*36mm for choose
Voltage	110V/ 60HZ or 220V/50HZ for choose

[diode laser 755 808 1064](#)

[diode laser hair removal machine](#)

[808nm diode laser](#)

[808nm diode laser hair removal machine](#)

[808nm diode laser manufacturer](#)

7 * 24 hour online service!
Welcome to consult!