

MLKJ

CUSTOMER SERVICE

15 YEARS FACTORY, 2 YEARS WARRANTY, 102 COUNTRIES, 60,000+ CUSTOMERS.

MLKJ—MAKE YOUR BEAUTY BUSINESS EASIER



15 years factory



2 years warranty



102 COUNTRIES



2 years warranty



14 inch
Screen Size



3000W
Input power



1-10HZ
Frequency



755nm 808nm 1064nm
Wavelength

>>Machine 14-inch large screen

>>3000W machine power to ensure the treatment effect

>>1-10Hz fast frequency and 15x25mm spot size ensures faster, smooth and effective treatment

>>808 single wave or 755nm/808nm/1064nm perfect triple wavelengths

>>Easy to operate Data Base system,can do the treatment by man mode and women mode,also different body part.To ensure a safe parameter for new operator

>> Long life time More than 40 millions shots gold laser diode module, anti high temperature.

350g lightweight **handle**, more ergonomic

Available in **black or white**





The handle weighs only 350g, which is convenient for treatment

>>12 pieces or 16 pieces Germany Dilas original laser bars,600/800W/1200W power is capable to meet all demands of hair removal on the whole body;

>>1-10Hz fast frequency and 15x25mm spot size ensures faster, smooth and effective treatment;

>Super sapphire touch cooling system ensures painless and comfortable treatment;

Hair removal principle

Make Your Beauty Business More Easier





The laser selectively acts on the melanin in the hair follicle, destroying the hair-growing area

Natural hair loss, prevent regeneration, and achieve the purpose of hair removal

Hair removal also stimulates collagen regeneration, shrinks pores and makes skin firm and smooth





755 nm for white skin (fine, golden hair removal);



808 nm for yellow neutral skin (brown hair removal);



1064 nm for black skin (black hair removal)

Handle Long life time 20-40 millions shots

Speed 808nm: Golden standard wavelength for all hair types

Alex 755nm: Specific effective for blonde hair, fine hair

Long Pulse 1064nm: Specific effective for dark, tanned skin best quality ipl shr opt laser/ nd yag /alexandrite laser hair removal machine price

Model	808- diode laser
Laser Type	808nm diode laser or 755/808/1064 3 wave
Display	14 inch touch screen system
Wavelength	808nm/755+808+1064
shots	20-40 million shots
Energy	10~150 j/cm2, adjustable
Frequency	1-10HZ
Cooling	Double TEC cooling
Power	3000W
Spot size	12*35mm or 12*20mm for choose
Voltage	110V/ 60HZ or 220V/50HZ for choose

Company Profile

1. Weifang Mingliang company has 15 years of beauty equipment manufacturing experience in beauty instrument.

It has been sold to 102 countries and serves over 600000 institutions worldwide Make

beauty business easier.

2.Support machine shell OEM □Machine system OEM□can add your own logo....

3.We have professional Production R & D department.The aluminum box packaging machine is sturdy and durable, with safety protection, helping your machine get home safely!

Packing

safe and thoughtful packaging service



Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable,
one-year warranty.

OEM&ODM service for distributor.

Tight packaging

Training: (Video+Manual+Online Service)
Can Keep You Operate It Easily.



3-5 business days delivery

Professional guide:

24 Hours Professional online customer service,

Contact us now
24 hours online!