



Has passed Medical CE, ISO13485, seriously
 Two-year warranty, maintenance forever.
 Our sales team will provide professional advice before you buy the machine.
 Free technical training for distributors is available.
 Operator video available for all buyers.
 Free technical to updating.
 On-line support by Skype, video on Youtube and email.



1. Laser technical, suits for all skin and hair types.
2. Handles: 1000W or 1200W, one spot size 12*20mm, the other 12*35mm
3. Fast treatment: 1-10Hz frequency, USA imported laser bars.
4. Continuous working 12h: Air+water+unique 1200W TEC cooling system, controls steady water temperature 24°C, ensure machine works

continuously all the day, even in summer without air-conditioner laser hair removal machine

1000W or 1200W or 1600W Laser hair removal machine

One minute cooling -27°C

Best **TEC Cooling** system
hair remover laser



Handle of Titanium Laser hair removal machine


- 1.12*20mm handle can you on small parts of the body, such as face hair removal and other samll place.
- 2.12*35mm can use at large parts of the body, such as back, arm and leg
- 3.With imported USA laser stack, strong energy, longest lifespan. the best laser in this line laser hair removal machine

350g lightweight **handle**, more ergonomic

Available in **black or white**



- >>Germany Emitter, strong energy
- >>1200W power of hair removal on the whole body;
- >>1-10Hz fast frequency
- >> Italy water pump, it can keep machine working 24 hours without stop.




Hair removal principle


Make Your Beauty Business More Easier



The laser selectively acts on the melanin in the hair follicle, destroying the hair-growing area



Natural hair loss, prevent regeneration, and achieve the purpose of hair removal



Hair removal also stimulates collagen regeneration, shrinks pores and makes skin firm and smooth

The laser contains four wavelengths output, has a wide range of applicability. It has a certain therapeutic effect on removing red blood streaks, varicose veins, anti-inflammatory, hair removal, whitening, and skin rejuvenation.



WALTZ PRO LASER

1	2	3

Screen System



The new 14-inch screen is clear
easy to operate.



OEM/ODM SEVRICE


3D LOGO with luxurious texture.

- 1) Touch Screen: 12.4 inch easy to operate.
- 2) 6 language for your choice.
- 3) Color for choose, also your LOGO could be put on screen and machine shell for free

Model	Laser hair removal machine
Laser type	Titanium Laser hair removal
laser bar	12 bar, 1200W, 10bar 1000W, imported from USA
Display system	12nch true color touch screen
Laser handle shots	40million times
Energy	10~150 j/cm2, adjustable
Pulse Duration	40~800ms adjustable
Frequency	1~10Hz
Cooling system	TEC condenser 1200W
	Air and close water circulation
	Treatment head with semiconductor
Spot size	cooling temprature adjustable
Crystal temperature	12*20mm, 12*35mm
Power requirement	-10~3°C
	AC220/110V, 50/60HZ

Custom Section


CASE design



LOGO design




SYSTEM design



Company Profile

OUR TEAM

There are more than 100 members of production team in our factory.





About mingliangkj:

Weifang Mingliang electronics Co., Ltd (abbreviation:MLKJ) is a highly professional and experienced manufacturer of beauty equipment in China,we have professional Production department,Quality Control department,Warehousing department and Sale&Service department.Our products are widely used in salon,clinic and home . Market around world ,including Europe ,North America,Asia and so on .our company has 13 years in beauty industry ,and pay attation to the quality and price of products

Product packaging

- 1.Weifang Mingliangkj electronics Co., Ltd (abbreviation:MLKJ)has 15 years in beauty industry
- 2.We have professional Production R & D department
- 3.Quality Control department,Warehousing department and Sale&Service department.

PACKING

safe and thoughtful packaging service



Built-in prevention
collision bubble

Two- year warranty for machine
handle as consumable,
one-year warranty

Tight packaging

Training:
(video +manual+online service)
can keep you operate it easily



3-5 business days
delivery

professional guide:
24 hours professional online
customer service