

**2021 Salon Queen**

**FASTER: 60% FASTER**  
**STRONGER: STRONGER POWER 40%**  
**BETTER RESULT**  
**SMARTER: 4K ANDROID SCREEN**

**FASTER, STRONGER, SMARTER**

1. Three wavelength diode laser.
2. Golden laser bars from German or USA improved 40,000,000+ longer lifespan.
3. Safe, Fast, Painless, permanent
4. For all skin and hair style hair removal
5. 14.0 inch true color touch screen with 6 skin colors.
6. Two models can be selected, single handle or double handle



## 2021 Salon Queen

**FASTER, STRONGER, SMARTER**

Most advanced TEC cooling system inside this machine to deliver a super good cooling results.  
24 hours working time. Sapphire material. Actual Pain-free experience!

- 1) 10 bars/ 12 bars/ 16 bars, 10-40 million shots.
- 2) Big spot 12\*20mm / 12\*35mm for fast hair removal.
- 3) Frozen ice cooling sapphire crystal, for painless hair removal.
- 4) High quality gold laser bar imported from Germany.
- 5) Medical handle as low as 350g easy to treatment.



**1 minute**  
and you're done

35mm

**FASTER**

### Screen system

1. 14 inch big touch screen, humanized designed.
2. Male/femal, body parts, 6 skin types for option.
3. 6 language systems, native language + whatever you want.
4. Free OEM program service(logo/system...)

Laser bar	Germany/USA imported, 8 bar, 10 bar, 12 bars, 16 bars
Wavelength	755nm 808nm 1064nm/ or single 808nm
Energy	0-150J/cm <sup>2</sup>
Frequency	1-10hz
Pulse width	40-800ms
Operative LCD Interface	14.0 TFT True Color LCD touch screen
Cooling system	Air and Close Water Circutation Treatment head with semiconductor cooling temperature adjustable
Power	4000W
Electrical source	220V/50HZ or 110V/60HZ

## Company Strength



- >>OEM your own machine body.
- >>OEM your own program software.
- >>OEM pretty machine colors.
- >>Print your LOGO on machine body and screen.

## Custom Section


### CASE design



### LOGO design



### SYSTEM design



### Certificate Display

# CERTIFICATE DISPLAY



# Packing

safe and thoughtful packaging service



## Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable,  
one-year warranty.

**OEM&ODM service for distributor.**

## Tight packaging

Training: (Video+Manual+Online Service)  
Can Keep You Operate It Easily.



## 3-5 business days delivery

Professional guide:  
24 Hours Professional online customer service,

