

755+808+1064 Technology.

* Permanent hair removal suitable For All Skin Hair Removal

* 1 session , 60%hair fall off







DIODE LASER

755/808/1064nm diode laser, for all type skin hair removal, painless



ADVANTAGE

- **PAINLESS:** 755/808/1064nm diode laser for all type skin hair removal
- **FASTER:** Large area spot sliding operation
- **NO TRAUMA:** There is no trauma to skin tissue
- **SAFETY:** To avoid the light of the deputy to reduce the difficulty of operation



1. 755nm+808nm+1064nm technology for all skin and hair style removal .
2. Effective for the hair follicles produce heat accumulation. Permanent painless hair removal.
3. Almost no skin scattering, no harm to the skin and sweat glands, no scar, no any side-effect
4. 3 in 1 cooling system: Air Cooling + Water Cooling + Compressor Cooling 3 in 1 system .24 hours working ability



Function of diode laser hair removal:

The 3 waves works in the same handle at the same time

755nm for white skin(fine, golden hair)

808nm for yellow/neutral skin

1064nm for black(black hair)

Super ice cooling effect, painless treatment is more comfortable






1. 14 inch big touch screen, humanized designed
2. Male/femal, body parts, 6 skin types for option.
3. English+your native language.
4. Free OEM program service(logo/system...)

The new **14-inch 4K** screen

Support system customization



Detailed specifications

Item	Vertical 755nm+808nm+1064nm diode laser
Laser type	Diode laser,10bars,12bars,16bars
Power of each bar	100w
Display system	14 inch true color touch screen
Wavelength	808nm/755nm/1064nm
Spot Size	12*20mm² 12*35mm²
Laser handle lifespan	Max 40,000,000 shots
Energy	10-150 J / cm2 adjustable (up to 150J/cm2 optional)
Pulse Duration	10~400ms adjustable
Frequency	1.0-10 Hz;
Cooling system	TEC semiconductor condenser+air+close water circulation
Handle Power	1000w/1200w/1600w
Machine Power	3500w
Electrical source	220V/50HZ or 110V/60HZ
Crystal temperature	-20~5°C
Machine temperature	24°C constant temperature
Power requirement	AC220V/110V 50~60Hz
Gross weight	80KG

Custom Section

LOGO design



SYSTEM design



Professional OEM ,ODM Services:

- Print any color .
- Add your logo
- Add any language into machine system.
- Design exclusive machine shell for you , form your own brand in market .
- Design new interface and system of machine , make it most convenient to you and your clients



15 Years Laser Beauty Decvice Manuafactor

Make your beauty business easier



15 Years
Laser Beauty Decvice
Manuafactor

After Service:

Considering the long distance between us with our clients, and in order to serve our clients much better, our company build a professional technology after service team.

1) Our technician will provide timely solution for any machine problem and prepare the documents for you within 24 hours.

2) You can also contact us by phone, online etc..

3) We offer whole training document and videos for the machine.

Our Showroom



Production Process



Warehouse spare parts



Parts assembly



Precision machining



Handle fabrication



Product assembly process



Quality inspection
of finished products



Product packaging



Packing

Safe and thoughtful packaging service



Tight packaging

The machine shall be made of waterproof materials and packaged

**Anti collision foam board
inside aluminum box**



3-5 business days delivery

Professional guide:

24 Hours Professional online customer service