



Has passed Medical CE, ISO13485, seriously  
 Two-year warranty, maintenance forever.  
 Our sales team will provide professional advice before you buy the machine.  
 Free technical training for distributors is available.  
 Operator video available for all buyers.  
 Free technical to updating.  
 On-line support by Skype, video on Youtube and email.



### Handle Details

1. Suits for all skin and hair types.
2. Handles: 1000W or 1200W, one spot size 12\*20mm, the other 12\*35mm
3. Fast treatment: 1-10Hz frequency, USA imported laser bars.
4. Continuous working 12h: Air+water+unique 1200W TEC cooling system, controls steady water

temperature 24°C, ensure machine works  
continuously all the day, even in summer without air-conditioner laser hair removal machine

### 1000W or 1200W or 1600W Laser hair removal machine

One minute cooling -27°C

Best **TEC Cooling** system  
hair remover laser

A hand wearing a white glove holds a black laser hair removal device with a white cooling head. To the left, a circular inset shows a digital thermometer displaying -27.0°C, indicating the cooling effect of the device.

#### Handle

- 1.12\*20mm handle can you on small parts of the body, such as face hair removal and other samll place.
- 2.12\*35mm can use at large parts of the body, such as back, arm and leg
- 3.With imported USA laser stack, strong energy, longest lifespan. the best laser in this line laser hair removal machine


**350g** lightweight **handle**, more ergonomic

Available in **black or white**



- >>Germany Emitter, strong energy
- >>1200W power of hair removal on the whole body;
- >>1-10Hz fast frequency

>> Italy water pump, it can keep machine working 24 hours without stop.




# Hair removal principle


Make Your Beauty Business More Easier



The laser selectively acts on the melanin in the hair follicle, destroying the hair-growing area



Natural hair loss, prevent regeneration, and achieve the purpose of hair removal



Hair removal also stimulates collagen regeneration, shrinks pores and makes skin firm and smooth

The laser contains four wavelengths output, has a wide range of applicability. It has a certain therapeutic effect on removing red blood streaks, varicose veins, anti-inflammatory, hair removal, whitening, and skin rejuvenation.

## Screen

1) Touch Screen: 12.4 inch easy to operate.



2) 6 language for your choice.

3) Color for choose, also your LOGO could be put on screen and machine shell for free


Model	Titanium Laser hair removal machine
Laser type	Titanium Laser hair removal
laser bar	12 bar, 1200W, 10bar 1000W, imported from USA
Display system	12inch true color touch screen
Laser handle shots	40million times
Energy	10~150 j/cm2, adjustable
Pulse Duration	40~800ms adjustable
Frequency	1~10Hz
Cooling system	TEC condenser 1200W
	Air and close water circulation
	Treatment head with semiconductor cooling temprature adjustable
Spot size	12*20mm, 12*35mm
Crystal temperature	-10~3°C
Power requirement	AC220/110V, 50/60HZ

## Custom Section


### CASE dedign



### LOGO design



### SYSTEM design



### Company Profile

## OUR TEAM

There are more than 100 members of production team in our factory.



## OUR COUNTRIES

All the products are taking with CE/ISO certification ,suitable for world market ,  
mainly used on North America ,  
South America Europe  
60, 000+ Customers Business development  
in 102+ countries...





# Customer visit



About mingliangkj:

1. Weifang Mingliangkj electronics Co., Ltd (abbreviation: MLKJ) has 15 years in beauty industry
2. We have professional Production R & D department
3. Quality Control department, Warehousing department and Sale & Service department.



# PACKING

safe and thoughtful packaging service



Built-in prevention  
collision bubble

Two- year warranty for machine  
handle as consumable,  
one-year warranty



Tight packaging

Training:  
(video +manual+online service)  
can keep you operate it easily



3-5 business days  
delivery

professional guide:  
24 hours professional online  
customer service