



OEM / ODM Service

Three wavelength diode laser

Safe, Fast, Painless, permanent
For all skin and hair style hair removal

Why choose our Titanium diode laser

- 1) Using TEC condenser, 1 minute cooling□24 hours continuously working
- 2) High power 1200w/1800w, strong energy, good hair removal effect
- 3) 2 years warranty of the machine
- 4) Painless, comfortable, and ice-feeling hair removal
- 5) laser hair removal machine price, Good after-sale service

Diode laser

hair removal machine

Safe • Fast • Painless • permanent



- *.808nm diode laser allows fast repetition rates up to 10Hz (10 pulses per second), fast hair removal for large area treatment.
- *.755nm+808nm+1064nm 3 wavelength , more suitable for all skin color hair removal treatment.
- *.1800w highest handle power, high laser energy density output up to 120J/cm²
- *. Effectiveness. Maximum efficiency to achieve freezing and painless hair removal treatment.



Handle features of Diode laser hair removal :

- »»USA laser bar, 10/15 bars, high power 1200/1800w
- »»Super Cooling effect: Sapphire Temperature-5~3°C. Effectively reduce the painful in the treatment and make
- »»Italy Water Pump: more better for laser water circle, take away heat, longer life time.
- »»Two water filters:two food grade exchange resin,can ensure the water quality for circulation

ULTRA-LOW
Temperature
-31°C

Ultra low temperature
protect skin
not burned by the laser



»»Super Cooling effect:Sapphire Temperature-5~3°C. Effectivly redcuce the painful in the treatment and make

»»Italy Water Pump:more better for laser water circle, take away heat, longer life time.

»»Two water filters:two food grade exchange resion,can ensure the water quality for circulation

Pain-free. The handle cools down to -31.3°C, makes treatment comfortable and effective.Continuous Contact Cooling .2 minutes reach -31.3°C, Painless hair removal 24 hours continuously working no any problem



Three Simultaneous Wavelengths in one Applicator

12mm*20mm / 12mm*35

Alex 755nm
Ideal for range of hair colors


Speed 808nm
Safe for darker skin types

YAG 1064nm
Perfect solution for darker skin

Mix Laser 755nm+808nm+1064nm
Multiple Laser Wavelengths and Technologies

LASER COMPARISON


【Other - Lasers】



- ✓ The original structure is not light enough.
- ✓ Big size.
- ✓ Short life.

VS


【2022-MLKJ-Lasers】



- ♥ Lighter weight.
- ♥ Smaller size.
- ♥ More advanced structure design.
- ♥ More advanced performance.

VS


【2022-MLKJ-Medical-Lasers】



- ♣ More advanced packaging technology.
- ♣ Higher energy densit.
- ♣ Lighter appearance.
- ♣ Longer life.

Treatment effect







Safe, Fast, Painless□permanent,For all skin and hair style hair removal
Good ice cooling, achieve pain free treatment,You will see good results after 3 treatments.

Suits for all skin and hair types treatment.

755nm for white skin (fine/ golden hair)hair removal.

808nm for yellow (natural) skin hair removal.

1064nm for black skin (black hair) hair removal.

Before and After ice platinum diode laser hair removal machine



Before

After



System The screen of titanium

- 14 inch big screen, quick touch□easy operate
- Male & femal, 6 body parts, 6 skin types
- 6 language options, your native language can be added
- Customarize service: logo, language , software.....

Product Configuration

Product Name	808 Diode Laser Hair Removal Machine
Laser type	755nm/808nm/1064nm
laser bar	10bar/12 bar/16 bar , imported from Germany/USA
Output power	Output power
Display system	14.0inch true color touch screen
Laser handle shots	10-40million times
Energy	10~150 j/cm2, adjustable
Pulse Duration	40~800ms adjustable
Frequency	1~10Hz
Crystal temperature	-5~3°C
G.W.□Box size	80KG□115*59*61cm

CERTIFICATE DISPLAY

Medical CE TUV ISO certification and more Complete certification materials



15 Years
Laser Beauty Device
Manufacturer

Make your beauty business easier

**Standardized
production**



**Professional
Production R & D
Sales Department**



**Mass production
of various styles**



Packing

safe and thoughtful packaging service



Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable,
one-year warranty.

OEM&ODM service for distributor.

Tight packaging

Training: (Video+Manual+Online Service)
Can Keep You Operate It Easily.



3-5 business days delivery

Professional guide:

24 Hours Professional online customer service,

Welcome to inquire more product details!
7X24 hours online service!