

**New  
arrivals**

**EXFU**

**SIMPLE . SAFE . ENJOY**  
New experience of hair removal



**On sale! FDA approved medical painless and permanent clinical hair removal treatment machine**

**Advantages**

- \* USA or Germany imported laser bar 10bars/15bars
- \* More than 50 million shots , more than 3 years don't need to change new handle.
- \* 3 waves 1064nm +808nm + 755nm, 3 in 1 all skin type can be used



# EXFU VIOLIN Portable Hair Removal Laser



Simple • Safe • Enjoy  
Redefine hair removal equipment



one-button start



Ice hair removal



super power



40million shine

## Products Description

# Ingenious details I am better than others

Product detail  
layout



## Surround light strip

Cool lighting effect  
not dazzling



## Newest design handle 0.31kg

One minute cooling  
Customizable glowing logo



## One-of-a-kind styling

Ingenious production  
focus on details



### **About Handle**

1200W/1800W big power for free choice

12\*24 or 12\*36mm spot size

\*285g Medical handle, light weight, free quick slide treatment

\* With indicator light, to show working condition(on machine & handle), safely use

**1 minute quick frosting, comfortable and painless treatment experience**





**Two colors, two spot sizes are optional**



Suitable for any unwanted hair on areas like face, arms, armpits, chest, back, bikini, legs...

755+808+1064nm, suitable for permanent hair removal of all skin types




**ALEX 755nm**  
**For white skin**  
(fine, golden hair removal )



**SPEED 810nm**  
**For yellow neutral skin**  
(brown hair removal)



**YAG 1064nm**  
**For black skin**  
(black hair removal)



Laser Type	Germany/USA imported, 8---12bars, 800W---1200W
Display	14 inch 4K touchable screen
Wavelength	808nm or 755nm 808nm 1064nm
shots	50 million shots
Energy	10~150 j/cm2, adjustable
Frequency	1-10HZ
Cooling	High Speed Double TEC coolingAir and Close Water Circulation Treatment head with semiconductor cooling temperature adjustable
Power	3500W
Spot size	12*24mm or 12*36mm for choose
Voltage	110V/ 60HZ or 220V/50HZ for choose

[diode laser 755 808 1064](#)

[diode laser hair removal machine](#)

[808nm diode laser](#)

[808nm diode laser hair removal machine](#)

[808nm diode laser manufacturer](#)

**7 \* 24 hour online service!**

**Welcome to consult!**