

NEW ! Technology



Free to be yourself

1 minute of painless hair removal,
Feeling the comfort and coolness that
has never been seen before.


14-inch screen

2 year warranty + work 24 hours



Diode laser hair removal machine Details

- 1.) Safe permanent hair removal on all skin types
- 2.) Frozen ice cooling sapphire crystal, for painless hair removal.



1 minute
and you're done

35mm {

FASTER

Diode laser hair removal machine handle power

spot size 12*20mm, 10 bars 1000w / 12 bars 1200w.

spot size 12*35mm, 16 bars 1600w.


Handle Details

Three Wavelengths Work Togher




12*20nm

755nm Laser
808nm Laser
1064nm Laser



12*35nm

755nm Laser
808nm Laser
1064nm Laser



One minute cooling -21°C


Best **TEC Cooling** system hair remover laser



***With special cooling technology(TEC-cooling),** cool the skin and protect skin from being hurt and reach

a very safe and comfortable *For permanent hair removal , suitable for all skin colors.

Pain free! the fastest hair removal technology, most popular! Suits for all skin and hair types treatment.



The 3 waves works in the same handle at the same time

1000w,1200w ,1600w handle

755nm for white skin(fine, golden hair)

808nm for yellow/neutral skin

1064nm for black(black hair)

Stuit to any color of skin



Application:

Elight for Skin Rejuvenation, Skin Tightening, Wrinkle Removal, Acne Removal, Pigment Removal, Vascular Removal, Breast Lifting, Age Spot Removal etc.

808 Hair Removal treatment pictures



Before and After

Treatment comparison



Screen Image


10.4 inch touch screen easy to operate.



1. 14 inch big touch screen, humanized designed
2. Male/female, body parts, 6 skin types for option.
3. English+your native language.
4. Free OEM program service (logo/system...)

The new **14-inch 4K** screen

Support system customization



Size Information

Item	Vertical 755nm+808nm+1064nm diode laser
Laser type	Diode laser,10bars/12bars/16bars
Power of each bar	50w
Display system	14 inch true color touch screen
Wavelength	808nm/755nm/1064nm
Spot Size	12*20mm²/12*35mm²
Laser handle lifespan	808nm:At least 10,000,000-40,000,000 shots
Energy	10-150 J / cm2 adjustable (up to 150J/cm2 optional)
Pulse Duration	40~800ms adjustable
Frequency	1.0-10 Hz;
Cooling system	TEC semiconductor condenser+air+close water circulation
Handle Power	1000w/1200w/1600w
Machine Power	2000w
Electrical source	220V/50HZ or 110V/60HZ
Crystal temperature	-10~3°C
Machine temperature	27~31°C

Power requirement AC220V/110V 50~60Hz

Gross weight 95KG

Our factory

1.Weifang Sunshinekj electronics Co., Ltd (abbreviation:MLKJ) is a highly professional and experienced

manufacturer of beauty equipment in China,has 13 years in beauty industry

About Us

We Are 13 Years

Professional high-tech beauty equipment manufacturer in China.

潍坊明亮电子有限公司

坚守客户价值不动摇·让客户满意

Stick firmly to customer's value to make them feel satisfied

坚守员工价值不动摇·让员工成长

Hold Fast to employees' value to let them develop



Mingliangkj in 2007, Through 13 years ,we have built reliable Production ,Quality Control ,Warehousing and Sale&Service department.

Products around world ,including Europe ,North America, Asia and so on .more than 600 clients in more, than 100 countrys all over the world



NEW





2.We have professional Production R & Ddepartment,
Can provide technical support 2 year warranty

Research and Development

We have professional Production R & D department.
From design research and development to production, every step is strictly checked to ensure product quality.



CAD and PCB drawing



Electrical schematic diagram
and preparation procedures



Ammeter test



Install the motherboard



Assemble the hardware



Leave the factory after
passing the inspection



Packing And Delivery

1



Print Logo



Check accessories before packing

2



Wiping and Wrapping machine



Rigorous inductive packing

3



Reminder identification



Fast delivery