



# Picosecond laser

## Features picosencond laser

- >> **No injury** to skin and hair follicle; **no risk** of scarring.
- >> Instantaneous blasting high laser technology, international standard of production, technical test strictly.
- >> Imported stone **Q-switch cassette** mechanism, the entire solid laser, without replacing Q-switch.
- >> **Painless** treatment, little side-effect.



# HANDLE-ADVANTAGE



## specification

- **Multiple choice**  
fixed 1064nm & 532nm, adjustable 1064nm & 532nm (adjust 1-7 mm) for tattoo removal, nevus removal etc.
- **Multifunction**  
1320nm for skin rejuvenation
- **Indicator light**  
Dot position is the indicator light position dot more accurate



Adjustable  
532nm



Adjustable  
1064nm



Black doll  
1320nm



Fixed  
755nm



Fixed  
532nm



Fixed  
1064nm



Six heads adjust spot size from 1mm to 7mm.



Adjustable 1064nm/532nm, fixed 1064nm/532nm/1320nm/755nm.

## Working Principle



- \* Fixed 1064/532nm used for tattoo removal, lipline removal, eyebrow removal, Nevus of Ota removal, fungus of nail removal.
- \* Fixed 1320nm used for skin whitening, pore shrink, skin lifting.
- \* Fixed 755nm used for skin whitening, remove yellow skin, chloasma, age pigment
- \* Adjustable 1064/532nm used for big area quick treatment, spot size 1-7mm adjustable.



Professional Screen, Easy operation



8.4 inch true color big touch screen, super cool touch experience  
 6 language for your choice, special language can be added  
 OEM service are accepted, such as machine colors style

## Size Information

APPLICATION	1)Tattoo removal 2)Eyebrow embroidery removal 3)Eyeline removal 4)Freckles removal 5)Skin rejuvenation 6)Lipline removal 7)Pigment treatment 8)Whitening
wavelength	1064nm&532nm&755 nm &1320nm &1064nm(Adjustable )&532nm(Adjustable )
Pulse energy	1-1500MJ/CM
Width of Pulse	0-10ns
Frequency	1-10HZ
Light spot	1-7mm
Power supply:	220V, 6A or 110V, 12A
color	Blue and black color
Packing method	Aluminum Packing
N.W	20kg
G.W	30kg
Machine	35cm*45cm*35cm(L*W*H)
Aluminum box	46*49*60cm(L*W*H)



Plastic foam:6cm



strong and beautiful  
aluminum alloy case



N.W 20KG



G.W 30KG

**Our factory**



# 15 Years Laser Beauty Device Manufacturer

- High Feedback  
Top10 Supplier
- OEM & ODM  
SERVICE

## Premium OEM Factories

High-performance manufacturing capacity  
R&D capability for customization  
Professional certifications and approvals

We have professional Production R & D department, Can provide technical support 2 year warranty



# Custom Services

Customized service to meet your needs




CUSTOM SCREEN



MACHINE COLORS



MACHINE SYSTEM



TROLLEY ALUMINUM BOX



PHONE HOLDER