

# 808 A5

808nm diode laser A5  
permanent hair removal





**Different spot size** Handle color optional






1. High power: 1000w
2. USA imported laser bars, has longer lifetime
3. Big spot sizes: 15\*25mm
4. Three wavelength in one, 755nm/808nm/1064nm

## Bar function

3 kinds of wavelength function




-  755 nm for white skin (fine, golden hair removal );
-  808nm for yellow neutral skin (brown hair removal);
-  1064nm for black skin (black hair removal)

# Working Principle

**Triple wavelength** laser work together

Suits for all skin and hair types



- **755nm for white skin** (fine, golden hair removal )
- **808nm for yellow neutral skin** (brown hair removal)
- **1064nm for black skin** (black hair removal)

**Machine has 3 waves laser bar, suitable for all skin and hair types, including tanned skin.**

\*755nm for light fine hair removal on white skin

\*808nm for natural hair removal on medium skin

\*1064nm for black hair removal on dark skin

# Screen display



# Stuit to any color of skin



## Application:

- 808 for Permanent Hair Removal

## Before&After



|                    |  |
|--------------------|--|
| Product Name       | Weifang Sunshine Diode Laser 1000w Portable Diode Laser Epilation Triple Wavelength Diode Laser  |
| Mode               | Laser 808 A5   |
| Laser type         | Germany Dilas laser emitter  |
| Display system     | 8.4inch 24 color multi-color touch screen  |
| Laser handle shots | 10-40million shots   |
| Wavelength         | 755/808/1064nm   |
| Power              | 1000w  |
| Energy             | 1-150J/cm <sup>2</sup> adjustable  |
| Pulse duration     | 1-300ms or 1-30ms adjustable   |
| Frequency          | 1.0-10 Hz  |
| Cooling system     | Air and Close Water Circulation Treatment head with semiconductor cooling temperature adjustable |
| Electrical source  | 220V/50Hz or 110V/60Hz   |
| Spot size          | 15*25mm  |

|                   |                     |
|-------------------|---------------------|
| Power requirement | AC220V/110V 50-60Hz |
| Package           | N.W 30KG, G.W 50KG  |

## OUR SERVICE

# About Us

## We Are 13 Years

Professional high-tech beauty equipment manufacturer in China.

**潍坊明亮电子有限公司**

坚守客户价值不动摇·让客户满意  
Stick firmly to customer's value to make them feel satisfied

坚守员工价值不动摇·让员工成长  
Stick firmly to employees' value to let them develop



Mingliangkj in 2007, Through 13 years ,we have built reliable Production ,Quality Control ,Warehousing and Sale&Service department.

Products around world ,including Europe ,North America, Asia and so on .more than 600 clients in more, than 100 countrys all over the world











Professional OEM ,ODM Services:

- Print any color .
- Print your logo on the machine .
- Add any language into machine system.

## FAQ

Q1. Warranty of machine and fittings.

A1:We are 10 years factory for laser beauty equipment , offer 2 years warranty for whole machine, During the warranty time ,we will get everything done for you .

Q2. How to transport?

A2: We offer door to door services by air or by express ( DHL/UPS/TNT etc)

Q3. What is delivery time?

A3: We have enough stock for the machine ,and all the machine can be sent within 3 days after received the payment:

Q4. If I do not know clearly how to use the machine ,how you can help me?

A4: when sending the machine to you ,we will send the User Manuel and DVD for you ,.and also we guarantee 2 years for whole machine ,when you receive the machine ,we will tell you how to use and how to solve problems .

Q5.Technology supports?

A5: Our technology department will offer 24 hours service. help finding the problem ,and show photos or video to solve that.All technical documents and fitting will be sent together with the machine.

Q6. Payment terms?

A6: T/T, Western Union,Alibaba Trade Assurance directly etc

Q7. After-Sale Service?

A7: The insurance will be purchased before shipment, avoid the loss from rough transportation.During the warrenty, the fitting will be replaced for free ;although overdued ,we will replace the fittingfor you at the bottom cost.

Certifications



# Our certificate

All the process of the producing is under ISO 13485 Quality system and match with CE certification request.



BV-France's most authoritative certification body BV Group certification



TUV-Germany's most authoritative certification body Rheinland certification



SGS-Switzerland's most authoritative certification body SGS certification



## Feedback

# Customer feedback



## Packaging & Shipping

# PACKAGING



Built-in prevention  
Collision bubble



Tight packaging



3-5 business days  
delivery