



DIODE LASER HAIR REMOVAL MACHINE

- SUPER ICE PAINLESS EXPERIENCE
- PERMANENT HAIR REMOVAL
- COMFORTABLE HAIR REMOVAL

1min} Fast and painless hair removal
One minute cooling -21°C

Four advantages

1.3 waves 1064nm + Diode 808nm + 755nm, 3 in 1 all skin type can be used


High power: NEW 1000W/ 1200W /1600W handle for options

2.Big spot size 15*25mm, 12*35mmface & body hair removal solution!

3.Cooling system: Unique Dual- TEC cooling system, most effective to ensure machine work all day, 24hr no down time.

4.Long life: double life support guarantee


3 in 1 all skin type can be used



755 nm for white skin (fine, golden hair removal);



808 nm for yellow neutral skin (brown hair removal);



1064 nm for black skin (black hair removal)

ice platinum diode laser hair removal machine.

- No pigmentation. Suitable for any kind of skin;
- Suitable for any kind of skin ;
- Safe and Fast.
- International Hair Removal Golden Standard;
- The optimal laser wavelength;

TEC cooling system

One minute cooling -21°C

Best **TEC Cooling** system
hair remover laser



Cooling system: Unique Dual- TEC cooling system, most effective to ensure machine work all day, 24hr no down time.

handle weighs only 350g

Available in **black or white**



Big spot size: The handle weighs only 350g! 15*25mm, 12*35mm face & body hair removal solution!

working principle

Hair removal principle

Make Your Beauty Business More Easier



The laser selectively acts on the melanin in the hair follicle, destroying the hair-growing area

Natural hair loss, prevent regeneration, and achieve the purpose of hair removal

Hair removal also stimulates collagen regeneration, shrinks pores and makes skin firm and smooth



Handle of diode laser hair removal machine: Quick cooling, painless treatment.



waves laser combines 755nm 808nm 1064nm, suits for all skin and hair types treatment.


755nm for white skin (fine/ golden hair) hair removal.

808nm for yellow (natural) skin hair removal.

1064nm for black skin (black hair) hair removal.

Before and After ice platinum diode laser hair removal machine

Treatment effect comparison



Application: Treatment effect comparison

ICE Platinum Diode Laser Hair Removal Machine for safe & permanent hair removal on all skins

Laser wavelength/type	ice platinum diode laser hair removal machine price laser 755/808/1064
Power	3000W;
Laser energy output	0-150J/cm2 (adjustable)
Laser pulse width	10-800ms(adjustable);
Pulse output frequency	1-10Hz;
Spot size	15*25mm ² /10*20mm ² option
Operative LCD Interface	10.4TFT True Color LCD touch screen
Cooling system Laser bar:	Water+air+TEC condenser 10 or 12 PCS bar option
Machine Size	105*40*40cm
Package size:	115*59*61cm
Net weight	35KG
Electrical source	220V/50HZ or 110V/60HZ

Comments from buyers

Screen for ice platinum diode laser hair removal machine

About the Shipping

**We can offer the door to door services
by air or by sea** just depend on your actual request.

Such as DHL,UPS,TNT,FEDEX...



Packing

safe and thoughtful packaging service



Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable,
one-year warranty.

OEM&ODM service for distributor.

Tight packaging

Training: (Video+Manual+Online Service)
Can Keep You Operate It Easily.



3-5 business days delivery

Professional guide:
24 Hours Professional online customer service,

Delivery time:	3 working days.
Delivery method:	Express door to door service, such as DHL, UPS, FedEx, TNT, etc.
Packing:	Aluminium box with foam