

Power upgrade

Make your hair removal faster



Four advantages


1.3 waves 1064nm + Diode 808nm + 755nm, 3 in 1 all skin type can be used

High power: NEW 1000W/ 1200W /1600W handle for options

2.Big spot size 15*25mm, 12*35mmface & body hair removal solution!

3.Cooling system: Unique Dual- TEC cooling system, most effective to ensure machine work all day, 24hr no down time.

4.Long life: double life support guarantee



diode laser hair removal machine.

- No pigmentation. Suitable for any kind of skin;
- Suitable for any kind of skin ;
- Safe and Fast.
- International Hair Removal Golden Standard;
- The optimal laser wavelength;

Our vs Other

 ✓ The screen of the handle does not freeze, and the capacitive screen system is operated by sliding	 ✗ Controller screen freezes, single-point operation
 ✓ 350g, smaller and lighter, more convenient for treatment	 ✗ The industrial handle is large and heavy, which makes the healer tired
 ✓ Customizable single band cooling for one minute, no need to wait during treatment, continuous cooling improves efficiency by 50%	 ✗ The replacement head is easy to get dust and burn out, cooling is slow, and you need to wait during the treatment process.
 ✓ Handle cooling piece×3,It can truly cool down in one minute and work 24 hours a day.	 ✗ There is only one handle cooling piece, which takes a long time to cool down. You need to wait for the handle to re-cool during the treatment process.
 ✓ Customer feelings:Good,The treatment has a micro-needle feel and is relatively comfortable.	 ✗ Customer feelings:Poor,The treatment felt like micro-needle, and there was obvious heat pain I couldn't tolerate it after 20 seconds, so I stopped and started again.
 ✓ Treatment without waiting	 ✗ Need to cool again during treatment

Cooling system: Unique Dual- TEC cooling system, most effective to ensure machine work all day, 24hr no down time.



Big spot size: The handle weighs only 350g! 15*25mm, 12*35mm face & body hair removal solution!

Any time
Any where
You can control the machine

Ios
Android

Handle of diode laser hair removal machine: Quick cooling, painless treatment.

MULTI-SCREEN LINKAGE

HANDLE WITH LARGE SCREEN, FREE INTERACTION WITH THE MAIN SCREEN, NO DELAY,
CAPACITIVE SCREEN SYSTEM SLIDING OPERATION



STABILIZE



SMOOTH



HANDLE SCREEN



waves laser combines 755nm 808nm 1064nm, suits for all skin and hair types treatment.

755nm for white skin (fine/ golden hair) hair removal.

808nm for yellow (natural) skin hair removal.

1064nm for black skin (black hair) hair removal.

Before and After diode laser hair removal machine



Higher power compressor

Ensure the best cooling effect




20%



New filter

- Double filtering
- Ensure clean water quality
- No need to change frequently



New upgrade
Italian water pump

Lifespan increased by
500%

Application: Treatment effect comparison

Diode Laser Hair Removal Machine for safe& permanent hair removal on all skins

Laser wavelength/type	diode laser hair removal machine price laser 755/808/1064
Power	2000W;
Laser energy output	0-150J/cm2 (adjustable)
Laser pulse width	10-800ms(adjustable);
Pulse output frequency	1-10Hz;
Spot size	15*25mm ² /10*20mm ² option
Operative LCD Interface	10.4TFT True Color LCD touch screen

Cooling system Laser bar:	Water+air+TEC condenser 10 or 12 PCS bar option
Machine Size	105*40*40cm
Package size:	115*59*61cm
Net weight	35KG
Electrical source	220V/50HZ or 110V/60HZ

Comments from buyers

Screen for ice diode laser hair removal machine



Delivery time:	3 working days.
----------------	-----------------

Delivery method:	Express door to door service, such as DHL, UPS, FedEx, TNT, etc.
Packing:	Aluminium box with foam