




STRONGER FASTER SMARTER

Hair Removal











Say Goodbye to Unwanted Hair with Ease

looking for the best diode hair removal machine?



MAKE EVERY HAIR REMOVAL A PLEASURE

10 Advantages of Handle Cooling

 Turn on machine, handle could work , no need to wait	 Lowest temperature could reach -32 C	 Turn on machine, handle could work , no need to wait	 Really painless when make the treatment	 Protect the customers skin
 One minute hair removal fast and effective	 Ice painless treatment feeling	 Comfortable experience.	 Continue cooling	 Adjustable cooling level.

Our range of diode laser hair removal machines—including 808nm diode laser hair removal, triple wavelength diode laser, and smart diode laser hair removal—is designed for both clinics and salons. Whether you need a professional diode laser hair removal machine, a portable diode laser hair removal machine, or a laser depilation machine, we offer high-performance systems at competitive diode laser machine prices. Choose from models like the 808 diode laser hair removal machine, 808nm diode laser machine, and 3 wavelength diode laser hair removal devices. We also offer options for laser hair removal machine for sale, diode laser machine for sale, and laser hair removal equipment for commercial use. Optimize your clinic's performance with our laser hair removal machine for business, laser hair removal machine industrial, and top laser hair removal machines.

Trusted by Laser Experts Across the Word



US AGENT

Cooperation since 2023



UK AGENT

Cooperation since 2015



CANADIAN AGENT

Cooperation since 2020



Netherlands Agent

Cooperation since 2018



GERMAN AGENT

Cooperation since 2010



SWEDISH AGENT

Cooperation since 2009



DENMARK AGENT

Cooperation since 2020



FINLAND AGENT

Cooperation since 2020



AUSTRALIA AGENT

Cooperation since 2008



FRENCH AGENT

Cooperation since 2022

We've worked with clients worldwide since 2008, including many salon owners and distributors.

Contact us to visit a local demo site and see the results for yourself.

top commercial laser hair removal beauty equipment manufacturers



50000000 SHOTS!

STRONGER

FASTER


SMARTER


-32°C

ICE POINTPAINLESS
ONE MINUTE COOLING -25°C

Developed by Mingliang Technology and certified by FDA (USA), MDL (Canada), and CE (Europe),


this machine is the perfect choice for those who prioritize safety and quality.








MAXIMIZE YOUR ROI

Reliable technology. Proven results.
Zero hidden fees.

**2 Years
Warranty**

**Lifetime
Service**

**FREE
Free Spare Parts**

**Safe & Easy
to Use**

* **2 Years Warranty**


* **Lifetime Service**

* **Free Spare Parts - No Extra Cost**

* **Safe & Easy to Use**

* **Maximize Your ROI**

Reliable technology. Proven results. Zero hidden fees.



Customized AI system

Temperature Control System

24-hour laser protection system when powered on

The latest FAC technology

Effective energy stronger than normal model 2400 W machine .
Higher treatment efficiency and reduced energy loss during treatment



FAC: Energy transfer efficiency **up to 99% !**

EASILY ADJUSTABLE

TO ANYANGLE

Precision angle control for customized treatment positions

HANDLE SCREEN INTELLIGENT LINKAGE

The value can be adjusted by the handle,
control screen Convenient and fast operation



The handpiece features a large touchscreen for one click operation. Designed for 24hour continuous use, it offers ultra-fast cooling and truly painless hair removal.



- 808nm Wavelength - Targets deep follicles for precise hair removal
- Fast & Painless - Large spot size, smooth-glide treatment

- Safe for All Skin Types -Fitzpatrick I-VI compatible
- Sapphire Contact Cooling - Protects skin, enhances comfort
- Long-Lasting Results - Slows regrowth,fewer sessions needed

For all types skin hair removal

755 NM

The Power of
Diversity



755nm

808 NM

Up To Speed



808nm

1064 NM


Dedicated to Darker
Skin



1064nm

Enjoy full OEM and ODM customization starting with only one unit—perfect for small businesses and custom branding

DIMENSIONS



Contact us today to get the best laser hair removal machine price and discover why professionals worldwide buy diode laser hair removal machines from us

Detail presentation



Application: Treatment effect comparison

ICE Platinum Diode Laser Hair Removal Machine for safe & permanent hair removal on all skins

Product Parameter

Device Name	Diode laser hair removal machine
Model Number	V36
Wavelength	<input type="checkbox"/> 808nm <input type="checkbox"/> 755+808+1064nm <input type="checkbox"/> 755+808+940+1064nm
Screen size	14 inch 4K true color touch screen
Pulse Duration	1-300ms
Frequency	1-10hz
Spot size	<input type="checkbox"/> 12*24mm <input type="checkbox"/> 12*36
Energy	1-150J/cm2
Cooling	Compressor cooling+Water circulation+Air + Semiconductor + Crystal Ice
Voltage	<input type="checkbox"/> AC220V 50HZZ <input type="checkbox"/> AC110V 60HZ
Demension of machine	1140*450*460mm
Package	Aluminum box
Warranty	2 years for machine , 1.5 years for handle

Comments from buyers

Screen fordiode laser hair removal machine



High Feedback Top10 Supplier
OEM & ODM Professional Design



Authentication

FDA,NQA13485,CB certification
and more Complete certification
materials



60000+ Customers

We have professional after sale
team and we provide 7*24
services



2 Years Warranty

2 years warranty for each
machine, All questions will get
reponse within 24 hours



FINE AND SAFE PACKAGING



Delivery time:	7 working days.
Delivery method:	Express door to door service, such as DHL, UPS, FedEx, TNT, etc.
Packing:	Aluminium box with foam